



Product information

Weller®

WSD 81i (dry cleaner)

Code No. : **T0053297399**

Set
Power unit PUD 81i, 95 W, 230 V, with soldering iron WSP 80 (80 W, 24 V) with silver line heating technology and safety rest WDH 10 with brass wool, includes UK and EU cordset.

Technical data



This station is ESD safe.

Dimensions L x W x H:	166 x 115 x 101 mm (6.54 x 4.53 x 3.98 inch)
Power supply:	230 V 50/60Hz; 240/120 V - 50/60 Hz; 120 V 60 Hz; 100 V - 50/60 Hz;
Power consumption:	95 W
Protection class:	I, housing antistatic III, soldering tool
Fuse	T500mA (230V, 50/60 Hz)
Temperature range:	50°C - 450°C; 150°F - 850°F
Temperature accuracy:	± 9°C
Temperature stability:	± 2°C
Equipotential bonding:	Via 3,5 mm pawl socket on back of device

- **Easy operation:**
Integrated, automatic processes and fewer operating requirements. No calibration needed (IPC compliant).
- **Rugged housing:**
Made from high quality, tough, antistatic materials and low wear plug and socket connectors.
- **100% long-term performance:**
Platinum sensor technology gives precise temperature accuracy and control. Compared to other stations, the WSD 81i offers temperature stability and accuracy without variation over time.