

SAMSUNG

SafeVIEW

Simple & Secure

Providing a safe and secure environment for your baby.



VGA Resolution Camera and 3.5" Portable Monitor Package

SEW-3037W

Monitor (Parent unit) features

- 3.5" Large display screen monitor unit
- Battery level indicator
- Sleep mode to extend battery life
- Integrated flip stand and belt clip
- Quiet mode to remove white background noise
- Two-way talk button

Camera (Baby unit) features

- Elegant compact design
- High resolution camera
- Non-visible IR LEDs for safe night time monitoring
- Built-in mic and speaker for two-way talk



Pan, Tilt & Zoom
allows you locate and get close to the action



Interference-free
long range signal allows monitoring at up to 900ft*



Night Vision
allows you to see even in the dark



Two-way Talk
allows you to talk to and hear your baby



Remote Night Light
allows you to soothe your little one to sleep

VGA Resolution Camera and 3.5" Portable Monitor Package

SEW-3037W

The Samsung SEW-3037W is an easy to use wireless baby monitoring system consisting of a high resolution 3.5" LCD monitor and wireless "night vision" camera with non-visible IR LEDs ensure safe night time monitoring. The camera unit features VGA (640x480) resolution to provide crisp and clear image and built-in mic and speaker of the camera allows two-way talk and you can talk to and hear your baby.

The SEW-3037W ensures long range transmission up to 800ft, allows you to monitor your baby at a distance. The monitor unit has LED on its front panel which indicates the level of sound so that you do not miss sound from your baby. And the pan and tilt of the camera can be operated from a parent unit with the button on the monitor so that you can adjust the view remotely.

Up to 4 cameras can be expanded with a monitor unit, the SEW-3037W will be a perfect solution to care the safety of your baby.

Specifications

General	
Operating Frequency	2.4GHz
Transmitting Power	17dBm Max
Receiving Sensitivity	-88dBm
Type of Spread Spectrum	FHSS 15 channels
Type of Modulation	GSFK
Data Rate	3Mbps
Transmitting Distance	300m * Range depends on obstacles between the camera and the monitor
Operating Temp. / Humidity	-10~40°C / Less than 85%
Camera	
Imaging Device	1/5" CMOS
Total Pixel	640 x 480 (VGA)
Frame Rate	QVGA 20fps
Video Compression Format	MJPEG
White Balance	Auto
Lens Focal Length	3.0mm
Max. Aperture Ratio	F2.8
Angular Field of view	56°
Pan/Tilt	Pan 300° Tilt 100°
Min. Illumination	2 Lux without IR
IR	940nm, 5m
Speaker Out	max. 1 Watt
Power Consumption	320mA (without IR LED)
Other Special Feature	Night vision
LCD Monitor	
Display	Color 3.5" LCD
Resolution	320 x 240 (CIF)
Number of Camera Support	up to 4 cameras
Speaker Output	Max. 1 Watt
Power Consumption	Max. 450mA (without charging)
Battery	1100mAh, 4.5hr
Digital Zoom	2x
Special Feature	Auto scan/Stand by/VOX/Two way talk/Time display/Night light



The Eco mark represents Samsung Techwin's will to create environment-friendly products, and indicates that the product satisfies the EU RoHS Directive.

Design and specifications are subject to change without notice.



SAMSUNG TECHWIN CO., LTD.

701, Sampyeong-dong, Bundang-gu, Seongnam-si, Gyeonggi-do Korea 463-400
Tel : +82-70-7147-8741-8749, 8752-8760 Fax : +82-31-8018-3745
www.samsungsecurity.com www.samsungcctv.com

SAMSUNG TECHWIN AMERICA Inc.

100 Challenger Rd, Suite 700 Ridgfield Park, NJ 07660
Toll Free : +1-877-213-1222 Direct : +1-201-325-6920
Fax : +1-201-373-0124
www.samsungcctvusa.com


SAMSUNG TECHWIN EUROPE LTD.

Samsung House, 1000 Hillwood Drive, Hillwood Business Park
Chertsey, Surrey, UNITED KINGDOM KT16 0PS
Tel : +44-1932-45-5300 Fax : +44-1932-45-5325

TIANJIN SAMSUNG TECHWIN OPTO-ELECTRONICS CO., LTD.

No.11 Wei 6 Street, Micro-Electronic Industrial Park
Jingang Road, Tianjin, P.R. CHINA 300385
Tel : +86-22-23887788 Fax : +86-22-23887788

■ DISTRIBUTED BY



M.E-1208