

# VALUE-LINE by BEVCO®



Model V4507MG

## AVAILABLE COLORS:

**Black**

**Blue**

**Grey**

## V4 Series - Upholstered Seating

Bevco produces its VALUE-LINE SEATING series of products with the same care that all Bevco products receive. All VALUE-LINE products have been tested by an independent laboratory to assure they meet applicable ANSI/BIFMA X5.1 standards for quality, durability and safety.

### Important Standard Features – All Models

- Sturdy five legged base
- Easy-to-use pneumatic seat height adjustment
- Ergonomic waterfall seat for improved leg circulation
- Contoured back with durable scuff resistant back pan
- Tilt back with adjustable tension control
- #2 philips screwdriver required for assembly

### Upholstery

- BIFMA Class 1 rated Olefin fabric resists fading, pilling, punctures and moisture
- Meets flame retardant standards of California Technical Bulletin 117

### Additional Options

- Ergonomic height adjustable armrests with polyurethane arm pads.

Model	Casters or Glides	Seat Height Range	18" Adj. Footring Included	Base Size	WT
V4007MG	Mushroom Glides	16" - 21"	No	25"	24 lb.
V4007CC	Carpet Casters	17" - 22"	No	25"	26 lb.
V4007HC	Hard Floor Casters	17" - 22"	No	25"	26 lb.
V4307MG	Mushroom Glides	20" - 27.5"	Yes	27"	30 lb.
V4307CC	Carpet Casters	21" - 28.5"	Yes	27"	32 lb.
V4307HC	Hard Floor Casters	21" - 28.5"	Yes	27"	32 lb.
V4507MG	Mushroom Glides	23" - 33"	Yes	27"	30 lb.
V4507CC	Carpet Casters	24" - 34"	Yes	27"	32 lb.
V4507HC	Hard Floor Casters	24" - 34"	Yes	27"	32 lb.

### OPTIONAL ARMS: Bevco Model AV - Adjustable Arms (height adjustable)

Standard Dimensions: Seat: 18"W x 18"D x 2<sup>3</sup>/<sub>4</sub>" Thick. Back: 16"W x 15"H x 2" Thick. Seat Foam Density: 1.8 lb., 36 IFD. Control: Back tilt, 360 degree swivel, pneumatic height adjustment. Base: Black, reinforced plastic. Warranty: 3-years on all components. See Bevco guarantee for details.