



Model 9052X-S
with optional arms and casters



Model 9551M-E
with optional ESD casters



Model 9051L-E
with optional ESD casters
and ESD armrests



Model 9351L-S
w/optional arms and vinyl upholstery

BEVCO®

9000 Series

Deluxe Seating

- Standard
- Laboratory
- Static Control (ESD)
- Cleanroom
- Combination Static Control ESD / Cleanroom

Bevco Built-In Values

- Certified Class 10, 100, 1000 & 10,000 Cleanroom models.
- Static control (ESD) versions available.
- Exceeds ANSI/BIFMA Standards.
- 12-year “top-to-bottom” guarantee covers the entire chair. Lifetime guarantee on the pneumatic cylinder.



9000 Series from Bevco

BEVCO's 9000 Series of seating provides advanced ergonomic features and total body support for all-day comfort. With models designed specifically for general use, laboratory, static control (ESD) and cleanrooms, this top-of-the-line seating will fit most requirements. Featuring a large, comfortable waterfall seat and your choice of three large backrest sizes, these chairs offer around-the-clock reliability in a variety of workplace environments.

Each chair features heavy-duty construction, easy-to-use ergonomic chair controls, pneumatic seat height adjustment, 360-degree swivel, sturdy five-legged highly polished cast aluminum base, and mushroom glides. Optional casters include hard floor, carpet, interval brake (lock when not in chair) or reverse brake (lock when sitting in chair) designs. Static control(ESD) casters are also available.

The 9000 Series seat features resilient high-density foam for long lasting comfort. Backrest styles are uniquely shaped for full back support and come standard with a heavy-duty polypropylene back shell to protect the upholstery if the chair bumps into a desk or a workstation.

Desk height models come standard with a 5" pneumatic cylinder. Bench height models feature a taller 7.5" or 10" pneumatic cylinder and 20" diameter adjustable chrome footring. Each model is available with/without seat and back tilt functions. Tilt models have seats with a tilt range of 6" rearward and forward and backs that tilt 11° forward and 150backward.

BEVCO's reputation for outstanding value in ergonomic seating is backed by over 50 years of manufacturing. Made in the U.S.A., our products carry BEVCO's superior guarantee. It's not prorated, applies to a 24-hour day, and covers defects in material and workmanship for a full 12 years. Pneumatic cylinders are guaranteed for the lifetime of the chair.



Model 9351L
w/optional ESD casters

Model	Height Adjustment	Seat & Back Tilt Feature	Footring	Weight (lbs.)
9050M	15½" - 21"	No	No	30
9051M	15½" - 21"	Yes	No	31
9350M	19" - 26½"	No	Adjustable Chrome	37
9351M	19" - 26½"	Yes	Adjustable Chrome	38
9550M	21½" - 31½"	No	Adjustable Chrome	37
9551M	21½" - 31½"	Yes	Adjustable Chrome	38

Back Sizes: Medium (17-1/2" w x 16" h x 3" thick); Large (17-1/2" w x 19" h x 3" thick); X-tra Large (19-1/2" w x 22-1/2" h x 3" thick) Seat Size: (20" w x 18" deep x 3" thick) Large (22" w x 18" deep x 3" thick) To replace the standard medium size back with a larger size, replace the "M" in the model number with an "L" or "X".

Chair Class Codes (add to the end of the model number i.e. 9050M-S)		
Code	Static Control (ESD)	Clean Room
-S	No	No
-E	Yes	No
C4	No	Class 10,000
E4	Yes	Class 10,000
C3	No	Class 1,000
E3	Yes	Class 1,000
C2	No	Class 100
E2	Yes	Class 100
C1	No	Class 10
E1	Yes	Class 10

Important Standard Features – All Models

- Ergonomic seat with waterfall edge for greater leg circulation and comfort.
- Medium, large or extra-large (except ESD models) contoured backrests for excellent upper and lower back support.
- Easy-to-use pneumatic seat height adjustment with "lifetime" cylinder guarantee
- Polypropylene back shell for improved durability as compared to upholstered versions.
- Five leg polished aluminum base

Upholstery

- Standard fabric colors: Burgundy, Medium Blue, Royal Blue, Navy Blue, Black, Gray, and Green
- ESD fabric colors: Charcoal, Slate Blue, Navy Blue or Gray.
- Optional vinyl upholstery in Black or Blue.
- Top rated Conductive fabric in BIFMA Class 1 Rated for durability. (Abrasion resistance exceeds 250,000 Double Rubs).
- Meets flammability standards of California Tech. Bulletin 117.

Static Control (ESD)

- All ESD chairs include drop chain, ESD glides, ESD footring (on bench height models), ESD Fabric/Vinyl, and an ESD back shell, as well as other chrome-plated components
- ESD models are static dissipative with a resistance of 10⁵ to 10⁹ ohms when measured according to the ANSI/ESD STM12.1-2006 standards.

Cleanroom

- All Cleanroom models have been tested by an independent certification company***, and meet particular goals of Federal Standard 209.
- Available in Blue or Black Vinyl.

Options

- Heavy-duty dual wheel casters for hard floor and carpets with interval braking. (ESD or non-ESD casters are also available)
- Tri-level control with separate seat tilt and back tilt levers.
- Combination Static control (ESD)/Cleanroom models available.
- Choice of medium, large or extra-large (except ESD models) back sizes.
- "02" Control with separate levers for back and seat tilt.

* ANSI: American National Standards Institute, Inc. BIFMA: Business and Institutional Furniture Manufacturers Association. BIFMA standards include safety, durability and structural adequacy evaluations.

** Pneumatic cylinders have a lifetime guarantee in the chair originally installed.

*** IBR has tested and certified these chairs for Cleanroom use.



Model 9051M
w/optional ESD casters and vinyl upholstery

BEVCO