



Model 7500



Bevco Built-In Values

- Heavy duty construction
- Meets ANSI/BIFMA Standards*
- 12 year guarantee
- ESD and Class 10 Cleanroom models
- NEW! 7000 Series models are now available that meet CAL 133 Fire Retardant Standards



BEVCO®
7000 Series
**Ergonomic
 Industrial
 Seating**



Model 7601



BEVCO®

7000 Series

BEVCO's 7000 Series Polyurethane Seating is specifically designed for outstanding comfort and long lasting use in the toughest workplace environment. Built with extraordinary care, these durable chairs offer total body support with advanced ergonomic features that improve productivity and reduce worker fatigue. Our rugged self-skinned polyurethane seat and back resist stains and damage from punctures, grease, water, and chemicals. Ventilation ribs increase air circulation, comfort and ease of cleanup.

Each BEVCO 7000 Series chair comes standard with easy-to-use pneumatic height adjustment, waterfall seat, fully adjustable contoured back and 360 degree swivel. Models 7001, 7201, 7301, 7501, and 7601 come with an articulating seat and back tilt control for maximum ergonomic benefit.

Models 7000 and 7001 feature a five star reinforced plastic base with mushroom glides. Models 7200, 7201, 7600, and 7601 come standard with a black five legged 16 gauge tubular steel base, welded chrome footring and rubber cushioned metal glides. Models 7300, 7301, 7500 and 7501 feature a wider five star base with an 18" diameter adjustable chrome footring.

BEVCO's reputation for outstanding value in workplace seating is backed by over 50 years of manufacturing. Made in the U.S.A., our products carry BEVCO's superior guarantee. It's not prorated, applies to a 24 hour day, and covers defects in material and workmanship for a full 12 years! **

* ANSI: American National Standards Institute, Inc. BIFMA: Business and Institutional Furniture Manufacturers Association. BIFMA standards include safety, durability and structural adequacy evaluations.

** Pneumatic cylinders have a lifetime guarantee in the chair originally installed.

Important Standard Features

- Durable, contoured polyurethane seat and back with ventilated ribs for lasting comfort and support
- Easy-to-use pneumatic seat height adjustment with "lifetime" cylinder guarantee
- Sturdy five legged base in reinforced plastic with mushroom glides or tubular steel with rubber cushioned metal glides
- Fully adjustable back with heavy duty back bracket
- Metal components have scratch resistant top grade baked enamel finish
- Available in Blue, Gray and Black. ESD and CAL 133 versions in Black only.

Options


- ESD models are static dissipative with a resistance of 10⁵ to 10⁹ ohms when measured according to the ANSI/ESD STM12.1-2006 standards.
- 7000CR Series- Class 10 cleanroom polyurethane models (ie: model 7200CR)
- 7000ECR Series- ESD/cleanroom polyurethane models (ie: model 7600ECR)
- Dual wheel hard floor, carpet or interval braking ESD or non-ESD casters
- Single rubber wheel casters
- "O2" control with separate levers for seat and back tilt. (specify model with "O2" option, ie: 7502)
- Adjustable armrests with polyurethane arm pads. Available on tilt models only. Must be specified with chair order. May not be added later.
- Larger 20" diameter adjustable chrome footring for models 7300, 7301, 7500 and 7501
- Exclusive CAL 133 compliant seats and backs available for added protection from fire and emissions.

Model	Height Adjustment	Height Adj. W/Casters	Vertical Back Adj.	Horizontal Back Adj.	Tilt		Foot Ring	Base Type	Weight (lbs)
					Seat	Seat			
7000	15" - 20"	16" - 21"	2 1/4"	2"	-	-	No	Reinforced Plastic	28
7001	15" - 20"	16" - 21"	6"	Tilt	6° Rearward 6° Forward	11° Forward 15° Backward	No	Reinforced Plastic	30
7200	18" - 23"	20" - 25"	2 1/4"	2"	-	-	Welded Chrome	16 Gauge Tubular Steel	31
7201	18" - 23"	20" - 25"	6"	Tilt	6° Rearward 6° Forward	11° Forward 15° Backward	Welded Chrome	16 Gauge Tubular Steel	33
7300	19 1/2" - 26 1/2"	20 1/2" - 27 1/2"	2 1/4"	2"	-	-	Welded Chrome	Reinforced Plastic	34
7301	19 1/2" - 26 1/2"	20 1/2" - 27 1/2"	6"	Tilt	6° Rearward 6° Forward	11° Forward 15° Backward	Adjustable Chrome	Reinforced Plastic	36
7500	21" - 31"	22" - 32"	2 1/4"	2"	-	-	Adjustable Chrome	Reinforced Plastic	34
7501	21" - 31"	22" - 32"	6"	Tilt	6° Rearward 6° Forward	11° Forward 15° Backward	Adjustable Chrome	Reinforced Plastic	36
7600	23" - 28"	25" - 30"	2 1/4"	2"	-	-	Welded Chrome	16 Gauge Tubular Steel	31
7601	23" - 28"	25" - 30"	6"	Tilt	6° Rearward 6° Forward	11° Forward 15° Backward	Welded Chrome	16 Gauge Tubular Steel	34

Standard Dimensions: Seat: 18-1/2" Wide x 17" Deep x 1-1/2" Thick. Back: 16-1/2" Wide x 12-1/2" Deep x 1" Thick.

***ESD and CAL 133 models only available in Black**

Because dye lots vary, colors of actual product may differ slightly from those shown here.



Model 7600E
ESD chair with optional casters

