

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [15-06-0085](#)  
**Status:** **Active**  
**Overview:** Mini-Fit® BMI  
**Description:** Mini-Fit® BMI Plug Housing, 4.20mm Pitch Dual Row with Panel Mount Ears, PA Polyamide Nylon 6/6, UL 94V-2, 8 Circuits

**Documents:**

|  |  |
|--|--|
| <a href="#">3D Model</a>                                 | <a href="#">Packaging Specification PK-42474-001 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>                            | <a href="#">Test Summary TS-5556-002 (PDF)</a>             |
| <a href="#">Product Specification PS-45750-001 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>       |
| <a href="#">Product Specification PS-5556-002 (PDF)</a>  |  |




image - Reference only

**Agency Certification**

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

**General**

|                |  |
|----------------|--|
| Product Family | Crimp Housings   |
| Series         | <a href="#">42475</a>  |
| Application    | Power, Wire-to-Board, Wire-to-Wire   |
| Comments       | Current = 13A max. per circuit when header is mated to a receptacle loaded with <a href="#">45750</a> series terminals crimped to 16 AWG wire. . See Molex product specification PS-45750-001 for additional current derating information. |
| MolexKits      | Yes  |
| Overview       | <a href="#">Mini-Fit® BMI</a>  |
| Product Name   | Mini-Fit® BMI  |
| UPC            | 800754204477   |

**Physical**

|                               |                 |
|-------------------------------|-----------------|
| Circuits (maximum)            | 8               |
| Color - Resin                 | Natural         |
| Flammability                  | 94V-2           |
| Gender                        | Male            |
| Glow-Wire Compliant           | No              |
| Lock to Mating Part           | Yes             |
| Material - Resin              | Nylon           |
| Net Weight                    | 3.880/g         |
| Number of Rows                | 2               |
| Packaging Type                | Bag             |
| Panel Mount                   | Yes             |
| Pitch - Mating Interface      | 4.20mm          |
| Pitch - Termination Interface | 4.20mm          |
| Polarized to Mating Part      | Yes             |
| Stackable                     | No              |
| Temperature Range - Operating | -40°C to +105°C |

**Electrical**

|                               |     |
|-------------------------------|-----|
| Current - Maximum per Contact | 13A |
|-------------------------------|-----|

**Material Info**

|                 |            |
|-----------------|------------|
| Old Part Number | 42475-0811 |
|-----------------|------------|

**Reference - Drawing Numbers**

|                         |   |
|-------------------------|---|
| Packaging Specification | PK-42474-001                            |
| Product Specification   | PS-45750-001, PS-5556-002, RPS-5557-034 |

|   |  |
|---|--|
| <b>EU RoHS</b><br><b>ELV and RoHS</b><br><b>Compliant</b><br><b>REACH SVHC</b><br><b>Contains SVHC: No</b><br><b>Low-Halogen Status</b><br><b>Low-Halogen</b> | <b>China RoHS</b><br> |
|---|--|

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[42475Series](#)

**Mates With**

[15-06-0080](#) Mini-Fit® BMI Panel Mount Receptacle, [39-01-2080](#) Mini-Fit® Jr. Receptacle

**Use With**

[46012](#) Mini-Fit® Plus HCS Crimp Terminal, [5558](#) Mini-Fit® Crimp Terminal

This document was generated on 08/26/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**