

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [43030-0007](#)  
**Status:** **Active**  
**Overview:** Micro-Fit 3.0™ Connectors  
**Description:** Micro-Fit 3.0™ Crimp Terminal, Female, with Tin (Sn) Plated Phosphor Bronze Contact, 20-24 AWG, Bag

**Documents:**

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)  
[Product Specification PS-43045 \(PDF\)](#)

**General**

|                             |   |
|-----------------------------|---|
| Product Family              | Crimp Terminals                           |
| Series                      | <a href="#">43030</a>                     |
| Application                 | Power                                     |
| Crimp Quality Equipment     | Yes                                       |
| MolexKits                   | Yes                                       |
| Overview                    | <a href="#">Micro-Fit 3.0™ Connectors</a> |
| Packaging Alternative       | <a href="#">43030-0001</a> (Reel)         |
| Product Literature Order No | 987650-5984                               |
| Product Name                | Micro-Fit 3.0™                            |
| UPC                         | 800753755772                              |

**Physical**

|                                |                      |
|--------------------------------|----------------------|
| Gender                         | Female               |
| Material - Metal               | Phosphor Bronze      |
| Material - Plating Mating      | Tin                  |
| Material - Plating Termination | Tin                  |
| Net Weight                     | 0.061/g              |
| Packaging Type                 | Bag                  |
| Plating min - Mating           | 1.016µm              |
| Plating min - Termination      | 1.016µm              |
| Termination Interface: Style   | Crimp or Compression |
| Wire Insulation Diameter       | 1.85mm max.          |
| Wire Size AWG                  | 20, 22, 24           |
| Wire Size mm²                  | N/A                  |


**Electrical**

|                               |    |
|-------------------------------|----|
| Current - Maximum per Contact | 5A |
|-------------------------------|----|

**Material Info**

**Reference - Drawing Numbers**

|                       |   |
|-----------------------|---|
| Product Specification | PS-43045, RPS-43025-002, RPS-43045-003, RPS-43045-004 |
| Sales Drawing         | SD-43030-****   |



**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[43030Series](#)

**Mates With**

[43031](#) Micro-Fit 3.0™ Male Crimp Terminals

**Use With**

[43025](#) , [43645](#) Micro-Fit 3.0™ Receptacle Housings, [44133](#) Micro-Fit BMI™ Panel Mount Receptacle Housings

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

| Description                       | Product #                  |
|-----------------------------------|----------------------------|
| Hand Crimp Tool                   | <a href="#">0638190000</a> |
| Insertion Tool for Crimp Terminal | <a href="#">0638120800</a> |
| Extraction Tool                   | <a href="#">0011030043</a> |

This document was generated on 09/15/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**