

Twist drill sets DIN 338 type N, HSS ground



214 214



214 214 S



214 214 RO



250 214 TRO



Description	N		
	Article no. HSS-G	Article no. HSS-G	Article no. HSS-G TIN
19-piece set of twist drills DIN 338 type N Ø 1,0 mm up to 10,0 mm in increments of 0,5 mm in steel case	214 214	214 214 S	250 214 T
25-piece set of twist drills DIN 338 type N Ø 1,0 mm up to 13,0 mm in increments of 0,5 mm in steel case	214 215	214 215 S	250 215 T
41-piece set of twist drills DIN 338 type N Ø 6,0 mm up to 10,0 mm in increments of 0,1 mm in steel case	214 218	—	—
50-piece set of twist drills DIN 338 type N Ø 1,0 mm up to 5,9 mm in increments of 0,1 mm in steel case	214 217	—	—
19-piece set of twist drills DIN 338 type N Ø 1,0 mm up to 10,0 mm in increments of 0,5 mm in plastic case	214 214 RO	214 214 SRO	250 214 TRO
25-piece set of twist drills DIN 338 type N Ø 1,0 mm up to 13,0 mm in increments of 0,5 mm in plastic case	214 215 RO	214 215 SRO	250 215 TRO

