



# HEAD TORCHES

HIGH POWER  
CREE LED HEAD  
TORCHES

## T9610 LED HEAD TORCH 120 LUMENS


Compact and lightweight, the T9610 is a remarkably powerful head torch for its size.

### Specification:

- > High Power 120 Lumen Cree XR-E Q3 LED
- > 3 Lighting modes: high, dimmed, flash
- > One-handed rapid slide focus mechanism - spot (x1) to flood (x7)
- > Beam intensifying plano-convex optical lens
- > Robust high grade aluminium lamp body
- > Adjustable head lamp swivels through 90°
- > Water & dirt resistant, tested to IP64
- > Battery life: high - 5hrs, dimmed - 13hrs



120 LUMENS



Beam	Max Range	Weather Rating	Impact Resistant	Power Supply	Battery Life
Spot x1 : Flood x7	200m	IP64	1M	3 x AAA (not supplied)	Up to 13 hours



90° swivelling lamp body



## T9620 LED HEAD TORCH 200 LUMENS


Powered by a high performance Cree XM-L T6 LED, the T9620 is the ideal choice of head torch for when a greater level of light intensity is required.

### Specification:

- > High Power 200 Lumen Cree XM-L T6 LED
- > 3 Lighting modes: high, dimmed, flash
- > One-handed rapid slide focus mechanism - spot (x1) to flood (x7)
- > Beam intensifying plano-convex optical lens
- > Robust high grade aluminium lamp body
- > Adjustable head lamp swivels through 90°
- > Detachable head lamp & battery pack
- > Water & dirt resistant, tested to IP64
- > Battery life: high - 5hrs, dimmed - 12hrs



200 LUMENS



Beam	Max Range	Weather Rating	Impact Resistant	Power Supply	Battery Life
Spot x1 : Flood x7	250m	IP64	1M	4 x AA (not supplied)	Up to 12 hours



Clip to belt facility



## T9620R LED RECHARGEABLE HEAD TORCH 200 LUMENS


A rechargeable version of the T9620 head torch, providing up to 15hrs of light from a single charge.

### Specification:

- > High Power 200 Lumen Cree XM-L T6 LED
- > 3 Lighting modes: high, dimmed, flash
- > One-handed rapid slide focus mechanism - spot (x1) to flood (x7)
- > Beam intensifying plano-convex optical lens
- > Robust high grade aluminium lamp body
- > Adjustable head lamp swivels through 90°
- > Water & dirt resistant, tested to IP64
- > Battery life: high - 7hrs, dimmed - 15hrs



200 LUMENS



Beam	Max Range	Weather Rating	Impact Resistant	Power Supply	Battery Life
Spot x1 : Flood x7	250m	IP64	1M	2x Rechargeable 18650 Li-ion Batteries (supplied)	Up to 15 hours



NEW



Rechargeable

