



HIGH POWER LED LIGHTS

T9410 8 LED POCKET INSPECTION LIGHT 120 LUMENS

Stood upright, laid flat or suspended via its magnetic clip, the T9410 pocket inspection light provides super-bright flood beam illumination, ideal for close proximity hands free applications.


Specification:

- > 8 Super bright LEDs
- > Wide flood beam
- > 180° rotating magnetic pocket clip
- > Water & dirt resistant, tested to IP64
- > Battery life: 8hrs
- > Size: 160 x 26mm



NEW

120 LUMENS



| Beam | Weather Rating | Impact Resistant | Power Supply | Battery Life |
|-------|----------------|------------------|-----------------------|---------------|
| Flood | IP64 | 1M | 3x AAA (not supplied) | Up to 8 hours |



Rotating magnetic clip



T9710R 10W RECHARGEABLE LED FLOOD LIGHT 600 LUMENS

Powered by a high performance, state-of-the-art COB (chips on board) Epistar LED, the rechargeable T9710 flood light gives complete freedom to illuminate even the most remote of areas.


Specification:

- > High Performance 600 Lumen Epistar COB LED
- > Power: 10W
- > Wide 120° flood beam
- > Magnetic base
- > Vertical and horizontal rotation
- > Water & dirt resistant, tested to IP65
- > Battery life: 3hrs
- > Size: 147 x 168 x 240mm



NEW

600 LUMENS



| Beam | Weather Rating | Power Supply | Battery Life |
|------------|----------------|---------------------------------------|---------------|
| 120° Flood | IP65 | Rechargeable 7.4V 4.4Ah Li-on Battery | Up to 3 hours |



Magnetic base

