

WDR Outdoor Bullet Camera



- 1/3" 1.3MP(1305*1049) SONY Exmor CMOS
- High rate, long-distance, real-time transmission
- Defog, D-WDR, 8X zoom
- Motion detection, privacy mask
- Smart IR control
- Adopt new IR Array technology
- HD CVI/CVBS 960H Dual output
- Power supply: DC12V

Specifications

Image Sensor	1/3" 1.3MP SONY Exmor CMOS
Effective Pixels	1305(H)×1049(V)
Resolution	Digital:1280×720P(720P/60fps) ; Analog:700TVL
S/N Ratio	≥50dB (AGC Off)
Min. Illumination	0Lux@(F2.0, IR ON)
Scanning System	Progressive
Video Output	Digital: HD-CVI ; Analog: 1Vp-p Composite Output(75Ω/BNC)
Day&Night	EXTERN,COLOR, B&W, AUTO
White Balance	Auto
Defog	OFF/ON
DNR	2D NR
WDR	OFF/LOW/MIDDLE/HIGH
Privacy Mask	ON/OFF (16 Areas)
Motion Detection	ON/OFF (4 Areas)
IR LED	2pcs IR Array LEDs
Lens	3.6mm/6mm/8mm
IR Range	30m
Input Voltage	DC12V±10%
Current	300mA
Power Consumption	<4W
Weight	450g
IP Rating	IP66
Operation temperature	-10°C ~+50°C (14°F ~122°F)
Operation humidity	<85%RH (Non-condensation)

Dimensions

