

1.3 Megapixel IP Intercom System

With Touchscreen Monitor & Door Station



Megapixel quality with IP simplicity, the INTIPRKIT is an ideal single monitor/door station solution for residential applications. It features a vandal resistant aluminium door station with 1.3 megapixel camera; a 7" touchscreen indoor monitor; and 30m CAT5e ethernet cable and 2x 12VDC power supplies for installation.

The door station is operated simply via a single backlit button whilst the indoor monitor uses a touchscreen. The system supports door sensor and door strike integration, remote unlock, missed/placed/received call details, visitor audio/video messaging and group calling functions.

Specifications - INTIPMONB - Indoor Monitor	
Main Processor	Embedded Microprocessor
Operating System	Embedded Linux OS
Display	Resistive Touch 7" TFT LCD
Display Resolution	800 x 480
Video Compression	H.264
Audio Input	Omnidirectional Microphone
Audio Output	Embedded Loudspeaker
Bidirectional Talk	Yes
Internal Storage	4GB - 100 photos/50 videos (5 min. max) /50 video & audio messages
Ethernet	10M/100Mbps Self Adaptive
Network Protocol	TCP/IP
Power	12VDC
Power Consumption	Standby ≤ 1.5W / Work ≤ 7W
Work Environment	-10°C~+60°C / 10~90%RH
Dimensions	261 x 192 x 24.1mm (LxWx H)
Weight	1.0Kg

Specifications - INTIPRDSV - Door Station	
Main Processor	Embedded Microprocessor
Operating System	Embedded Linux OS
Door Station Camera	1.3 Megapixel CMOS Camera
Memory	128MB
Video Compression	H.264
Audio Input	Omnidirectional Microphone
Audio Output	Embedded Loudspeaker
Bidirectional Talk	Yes
Vandal/Weather Resistant	Vandal: Yes / Weather: Requires partial shelter (eaves, awning, etc.)
Ethernet	10M/100Mbps Self Adaptive
Network Protocol	TCP/IP
Power	12VDC
Power Consumption	Standby ≤ 1W / Work ≤ 10W
Work Environment	-10°C~60°C / 10~95% RH
Dimensions	141 x 100 x 16.8 mm
Weight	0.8Kg

Your Local Dealer