

REGAL WEALTH ENGINEERING LIMITED

ADD: SUZHOU REPRESENTATIVE OFFICE, 0203A1 1A SINGA PLAZA JINJIHU ROAD SUZHOU INDUSTRIAL PARK, P. R. CHINA

TEL: 86-512-62532393 FAX:86-512-62532690

Type:	6.0mm pro audio cable	Part No. : AC-039	
Spec. :	(28/0.12BC+PVC1.6)*2C+COTTON YARN+AL-FOIL+BD16*8/0.12TC+PVC6.0		
Construction:			
Conductor	Construction:	28/0.12mm (BC OFC)	
	DC Resistance(Max. at 20°C):	60.02 Ω /km	
Insulation	Material:	PVC	
	Color:	RED, WHITE	
	Diameter/Thickness:	1.60±0.10mm / 0.43mm	
Filler	Material:	COTTON YARN	
Drain Wire	Construction:	/	
Wrap	Material:	AL	
Shield	Construction:	16*8/0.12mm (TC OFC)	
	Coverage:	95%	
	DC Resistance(Max. at 20°C):	14.59 Ω /km	
Covering	Material:	/	
	Diameter:	/	
Jacket	Material:	PVC	
	Color:	TRANSPARENT BLACK	
	Diameter/Thickness:	6.0±0.20mm / 1.1mm	
Marking:	MICROPHONE CABLE		
Performance:			
Physical Properties	Jacket	Swing Test:	≥1500
		Tensile Strength(Mpa):	≥10.5
		Elongation	≥100%
	INSULATION	Swing Test:	/
		Tensile Strength(Mpa):	/
		Elongation	/
Electrical Performance	Capacitance pF/m	/	
	Characteristic Impedance(Ω):	/	
	RTED TEMPERATURE °C	/	
	VOITAGE V/DC	60/30	
	Withstand Voltage(KV AC/Min):	0.5	
	Frequency(MHZ)	/	
Attenuation(DB/M)	/		
Drawing:			
			