



- Description :** [IBM AT - ISA Extender : 3690-26](#)
- Length** : 5.6"
- Contacts** : 18 Contacts each side on .100" centers  
: 31 Contacts each side on .100" centers
- Test Points** : On each connector line
- Current Rating** : 5 amps at 10' F rise
- Voltage Rating** : 200 RMS or 300 VDC
- Receptacle Contacts** : Ni/Gold plated
- Material** : FR4 Epoxy Glass 2 oz Copper { MIL - P13949 type GF }
- NEMA Grade** : FR4
- UL Flammability Class** : 94V - 0