


Data Sheet

Type 360322

Illustration



see enlarged drawing at the end of the document

Product specification

- screw type terminal block, THR solderable, double solder pins
- direction of connection 90°
- wire protector
- color metal
- Tape & Reel packaging
- open construction, screw brought down by hand (transport safety)
- Connection data

RJ A / AWG 15 / 30 - 16

A / AWG 15 / 30 - 16

Data Sheet

Type 360322

Technical Data

General Data

Tightening torque SEV	0.5 Nm
Tightening torque UL	6 lb-in
Solder pin length	3.5 mm
min. number of poles	1
max. number of poles	1
protection category	IP 00

Connection data

 A / AWG	15 / 30 - 16
A / AWG	15 / 30 - 16

Material

terminal body material	CuZn
terminal body surface	Ni + Sn
screw surface	Zn Cr(VI)-frei/free
wire protector material	CuSn
wire protector surface	Sn
screw thread	M3

General

solderability	For THR products acc. to IPC/JEDEC J-STD-020D-MSL 1 For THT products max. 260 °C / 10 s
Tolerance	ISO 2768 -mH




Data Sheet

Type 360322

Illustration

Drawing



Data Sheet

Type 360322

PCB Layout

