

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [51021-0300](#)  
**Status:** **Active**  
**Overview:** [PicoBlade™ Connector System](#)  
**Description:** 1.25mm Pitch PicoBlade™ Wire-to-Wire and Wire-to-Board Housing, Female, 3 Circuits

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification PS-51021-023 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-51021-024 (PDF)</a>
<a href="#">Product Specification PS-51021-001 (PDF)</a>	<a href="#">Product Specification PS-51021-025 (PDF)</a>
<a href="#">Product Specification PS-51021-002 (PDF)</a>	<a href="#">Product Specification PS-51021-026 (PDF)</a>
<a href="#">Product Specification PS-51021-009 (PDF)</a>	<a href="#">Product Specification PS-51021-027 (PDF)</a>
<a href="#">Product Specification PS-51021-010 (PDF)</a>	<a href="#">Product Specification PS-51021-028 (PDF)</a>
<a href="#">Product Specification PS-51021-011 (PDF)</a>	<a href="#">Packaging Specification SPK-51021-001 (PDF)</a>
<a href="#">Product Specification PS-51021-022 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	Crimp Housings
Series	<a href="#">51021</a>
Application	Signal, Wire-to-Board, Wire-to-Wire
MolexKits	Yes
Overview	<a href="#">PicoBlade™ Connector System</a>
Product Name	PicoBlade™
UPC	800753575608

**Physical**

Circuits (maximum)	3
Color - Resin	Natural
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	34.175/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.25mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +85°C

**Electrical**

Current - Maximum per Contact	0.8A, 1A
-------------------------------	----------

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	SPK-51021-001
Product Specification	PS-51021-001, PS-51021-002, PS-51021-009, PS-51021-010, PS-51021-011, PS-51021-022, PS-51021-023, PS-51021-024, PS-51021-025, PS-51021-026, PS-51021-027, PS-51021-028,




image - Reference only

**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status**  
**Not Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[51021Series](#)

**Mates With**

[53261](#) 1.25mm Pitch PicoBlade™ Right Angle SMT Header, [53047](#) 1.25mm Pitch PicoBlade™ Vertical Thru-Hole Header, [53398](#) 1.25mm Pitch PicoBlade™ Vertical SMT Header, [53048](#) 1.25mm Pitch PicoBlade™ Right Angle Thru-Hole Header

**Use With**

[50058](#) Crimp Terminal, [50079](#) Crimp Terminal

RPS-51021-001, RPS-51021-002, RPS-51021-003,  
RPS-51021-004, RPS-51021-005, RPS-51021-006,  
RPS-51021-007, RPS-51021-008, RPS-51021-009,  
RPS-51021-010, RPS-51021-011, RPS-51021-013,  
RPS-51021-014, RPS-51021-018, RPS-51021-019,  
RPS-51021-020, RPS-51021-021, RPS-51021-023,  
RPS-51021-024, RPS-51021-025, RPS-51021-028,  
RPS-51021-030, RPS-51021-031, RPS-51021-032,  
RPS-51021-033, RPS-51021-034, RPS-51021-037,  
RPS-51021-038, RPS-51021-039, RPS-51021-040,  
RPS-51021-041, RPS-51021-042, RPS-51021-043,  
RPS-51021-044, RPS-51021-045, RPS-51021-046,  
RPS-51021-047, RPS-51021-048, RPS-51021-051,  
RPS-51021-052, RPS-51021-053, RPS-51021-054,  
RPS-51021-055, RPS-51021-056, RPS-51021-057,  
RPS-51021-058, RPS-51021-059, RPS-51021-060,  
RPS-51021-061, RPS-51021-062, RPS-51021-063,  
RPS-51021-064, RPS-51021-065, RPS-51021-066,  
RPS-51021-068, RPS-51021-071, RPS-51021-076,  
RPS-51021-078, RPS-51021-080, RPS-51021-081,  
RPS-51021-089, RPS-51021-092, RPS-51021-096,  
RPS-51021-097, RPS-51021-101, RPS-51021-102,  
RPS-51021-103, RPS-51021-104, RPS-51021-105,  
RPS-51021-107, RPS-51021-108, RPS-51021-112,  
RPS-51021-114, RPS-51021-117, RPS-51021-118,  
RPS-51021-121, RPS-51021-122, RPS-51021-123,  
RPS-53398-002, RPS-53398-037, RPS-53398-038  
SD-51021-002, SD-51021-005

Sales Drawing

This document was generated on 09/15/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**