

**PSEN ma1.4p-57/PSEN ma1.4-03mm/  
1unit  
Product number:  
506337**

<b>Product version:</b>	1.0
<b>Approvals:</b>	CE, cULus Listed, TÜV
<b>Sensor principle:</b>	magnetic
<b>Number of N/O:</b>	2
<b>Connection type:</b>	M8, 8pol. male
<b>Switching voltage:</b>	24 V
<b>Type of switching voltage:</b>	DC
<b>Assured switching distance:</b>	3.0 mm
<b>Assured release distance:</b>	12 mm
<b>Protection type, housing:</b>	IP6K9K
<b>Status indicator:</b>	With LED
<b>Design:</b>	square
<b>Width dimension:</b>	26.0 mm
<b>Height dimension:</b>	37.0 mm
<b>Depth dimension:</b>	18.0 mm
<b>Gross weight:</b>	77 g
<b>Net weight:</b>	32 g
<b>Ambient temperature:</b>	-10 - 55 °C