

## Embedded Plug & Play NVR




### LTN 87XX Series DVR's

#### Key features

- Third-party network cameras supported
- Up to 5 Megapixels resolution recording
- HDMI and VGA output at up to 1920×1080P resolution
- 4/8/16-ch network cameras can be connected with 25M/50M/100M incoming bandwidth
- Up to 2 SATA interfaces
- Plug & Play with up to 8 independent PoE network interfaces
- Support network detection, including network delay, packet loss, etc

#### Rear Panel of the 87XX Series NVR (Please note the 4 POE has only 4 RJ45 connectors)



1. Power Supply
2. Audio In
3. HDMI Interface
4. LAN Network Interface
5. Audio Out
6. VGA Interface
7. USB Interface
8. Ground
9. Power Switch
10. Network Interfaces with PoE Function

	LTN8704-P4	LTN8708-P8	LTN8716-P8
<b>Video/Audio input</b>			
IP video input	4-ch	8-ch	16-ch
Two-way audio input	1-ch, RCA (2.0 Vp-p, 1kΩ)		
<b>Network</b>			
Incoming bandwidth	25Mbps	50Mbps	100Mbps
Outgoing bandwidth	80Mbps		
Remote connection	128		
<b>Video/Audio output</b>			
Recording resolution	5MP/3MP/1080P/UXGA/720P/VGA/4CIF/DCIF/2CIF/CIF/QCIF		
Frame rate	Main stream: 50 fps (P) / 60 fps (N) Sub-stream: 50 fps (P) / 60 fps (N)		
HDMI/VGA output	1-ch, resolution: 1920 × 1080P /60Hz, 1600 × 1200 /60Hz, 1280 × 1024 /60Hz, 1280 × 720 /60Hz, 1024 × 768 /60Hz		
Audio output	1-ch, RCA (Linear, 1kΩ)		
<b>Decoding</b>			
Live view / Playback resolution	5MP/3MP/1080p/UXGA/720p/VGA/4CIF/DCIF/2CIF/CIF/QCIF		
Capability	4-ch@1080P	8-ch@720P, 6-ch@1080P	16-ch@4CIF, 12-ch@720P, 6-ch@1080P
<b>Hard disk</b>			
SATA	1 SATA interface for 1 HDD	2 SATA interface for 2 HDDs	
Capacity	Up to 4TB for each disk		
<b>External interface</b>			
Network interface	1 RJ-45 10 /100 /1000 Mbps self-adaptive Ethernet interface		
USB interface	1 × USB 2.0 and 1 × USB 3.0		
<b>PoE</b>			
PoE Interface	4 independent 100 Mbps PoE	8 independent 100 Mbps PoE	
Max. Power	50W	120W	
Standard	AF and AT		
<b>Others</b>			
Power supply	48V DC	220V AC	
Consumption (without harddisk)	≤ 10W		
Working temperature	-10 ° C ~ +55 ° C (14° F~131° F)		
Working humidity	10 % ~ 90 %		
Chassis	1U chassis	19-inch rack-mounted 1U chassis	
Dimensions (W × D × H)	445 × 290 × 45mm (17.5 × 11.4 × 1.8 inch)		
Weight (without hard disk)	≤ 1 Kg (2.2 lb)		