


Model Number: MW12CB072**TYPE** :Lead Acid Battery Charger**Electrical Data**

Input	Input Voltage/Frequency	230V/50Hz
	Input Power	11W
Output	Rated Charging Voltage	12V
	Rated Charging Current	720mA
	Rated Output Power	8.6VA
Resistance	Insulation Resistance	100M Ω (measured with 500V DC voltage)
Protection	Thermal Protection	Thermal fuse: cut off temperature:125 $^{\circ}$ C
	Withstand Voltage (Hi-Pot)	AC 3750V 50Hz for 1minute or AC4000V 2seconds

Mechanical Data

Supply Connection Type	-----			
Primary Turns & Wire Gauge	1550T/ Φ 0.13mm			
Diagram of transformer terminals: 	Secondary Turns & Wire Gauge			
	leading terminal	Wire No.	Gauge (mm)	turn (T)
	A-B	SWG24	0.55	85
Core Size	48mm \times 26mm			
Unit Weight (g)	486g			
Dimensions (mm)	85(L) \times 62(W) \times 88(H)			