

UL1061 - 26AWG PVC Hook-Up Wire

305m reel

pro-POWER



Specifications:

Conductor Material	: Tinned Copper
Conductor Size AWG	: 26
Conductor Area CSA	: 0.13mm ²
No. of Strands × Strand Size	: 7 × 0.16mm
Conductor Make-up	: 7 × 34AWG
Jacket Material	: Semi-Rigid PVC
Jacket Min. Average Thickness	: 0.25mm
Jacket Colour	: See Table Below
External Diameter	: 0.99mm
Voltage Rating	: 300V
Current Rating	: 4A
Operating Temperature Max.	: 80°C
Reel Length (Imperial)	: 1,000ft
Reel Length (Metric)	: 305m

Part Number Table

Description	Colour	Part Number
26AWG 7/34 UL1061	Black	PP000197
	Grey	PP000198
	White	PP000199

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com
www.farnell.com
www.newark.com
www.cpc.co.uk

pro-POWER