

TeraStation™ 1200

Network Attached Storage

BUFFALO™

TS1200D

Big Features in a Small Package

Buffalo Technology's TeraStation 1200 series (TS1200D) is a two bay storage solution with advanced business features and a strong Dual Issue CPU: perfect for small business users ready to migrate to Network Attached Storage or expand the capacity and features of their existing storage solution.

Users will be impressed with the TS1200D for its business-class feature set including support for RAID 0/1/JBOD, replication, and available capacities up to 8TB. The TS1200D is equipped with the Marvell Armada Dual Issue CPU processor with 512 MB of DDR3 RAM bringing together Buffalo's high performance hardware and architecture and delivering them in a cost-effective solution.

Want more protection? The TS1200D also comes with 10 free NovaStor® NovaBACKUP licenses. The TS1200D is available fully populated with 2, 4, 6, or 8TB capacities.



Features and Benefits

- Two bay NAS available in a Desktop version fully populated with 2, 4, 6, or 8TB capacities
- Powered by the latest Marvell Armada Dual Issue CPU processor
- 512MB of fast DDR3 memory installed
- Full-featured Network Attached Storage device
- Advanced RAID 1 technology offers immediate fault-tolerance out-of-the box
 - Or, users can opt for RAID 0 or JBOD depending on their storage needs
- Packed with rich backup features:
 - Replication
 - Scheduled Backup
 - NovaStor® NovaBACKUP® (10 licenses of NovaBACKUP® Business Essentials)
 - Hot Swap: Change drives in RAID 1 without down time
- WebAccess - easily open TeraStation™ files on a remote site or with Apps for Windows 8, iOS, Android, and Windows Phone 7 – 8
- 3 years warranty and VIP service included:
 - 24h* HDD exchange, no pre-payment required



TeraStation™ 1200

Network Attached Storage



TS1200D

Specifications

Hardware	
System	
CPU	Marvell Armada 370, Dual-issue 1.2GHz ARM
RAM	512MB DDR3
Internal Hard Drives	
Number of Drives	2
Drive Interface	SATA II, 3Gb/s
Hard Drive Capacities	1, 2, 3, 4TB
Total Capacities	2, 4, 6, 8TB
System	
Raid	0/1/JBOD
Hot Swap	Change drives in RAID without down time
HDD Encryption	Data protection: Data cannot be read on other machines
Interfaces	
LAN	
Standard Compliance	IEEE802.3ab / IEEE802.3u / IEEE802.3 Standard
Connector Type	RJ45
Number of Ports	1
Data Transfer Rates	10/100/1000 Mbps
USB	
Standard Compliance	USB2.0
Connector Type	USB type A
Number of Ports	1 x USB2.0
Data Transfer Rates	480Mbps
Protocol Support	
Networking	TCP/IP
File Sharing	SMB/CIFS, AFP, FTP/SFTP, NFS, HTTP/HTTPS
AD Integration	LDAP
Management	HTTP/HTTPS
Time Synchronisation	NTP
Other	
Supported OS	Windows® 8.1 (32/64bit), Windows® RT 8.1 (32/64bit), Windows® 8 (32/64bit), Windows® 7 (32/64bit), Windows® Vista™ (32/64bit), Windows Server 2012 (32/64bit), Windows Server 2008/R2 (32/64bit), Mac OS X 10.7, 10.8, 10.9
Dimensions	87x205x128mm
Weight	2,4kg
Operating Environment	5-35 C, 20-80% (non-condensing)
Power Consumption	Ave 26W / Max 48W (with no USB devices connected)
Power Supply	External, AC 100-240V, 50/60Hz
Backup	
Backup	Built in backup to USB storage or other Buffalo NAS based on rsync
Replication	Synchronise folders on two TeraStation
Time Machine	Time Machine target for multiple clients
NovaBackup Business Essentials	10 licenses of NovaBackup Professional backup software for Windows clients
Remote Access	
Web UI	via HTTP/HTTPS
FTP Server	FTP/SFTP
WebAccess	Android/iOS/Windows Apps, HTTP/HTTPS

Product Codes

TS1200D0202-EU
 TS1200D0402-EU
 TS1200D0602-EU
 TS1200D0802-EU



About Buffalo

Buffalo Technology is a leading global provider of award-winning storage, networking and multimedia solutions for the home and small business environments as well as for system builders and integrators. With more than three decades of networking and computer peripheral experience, Buffalo has proven its commitment to delivering innovative solutions that have put the company at the forefront of infrastructure technology.

© Buffalo Inc. 2014. BUFFALO logo, AirStation, Nfiniti, AOSS, TeraStation, LinkStation, DriveStation and MiniStation are either trademarks or registered trademarks of Melco Holdings Inc. or Buffalo Inc. Microsoft Windows and Microsoft logo are either registered trademarks or trademarks of Microsoft Corporation in United States and/or other countries. The names and logos of other companies mentioned herein belong to their respective owners. The information within this datasheet is subject to change without notice. All rights reserved. E & OE.