




# QUICK CONNECT CONNECTORS




## QUICK CONNECT<sup>®</sup> Connector with Cable Sleeve

- Moulded cable sleeve
- 4-point (quarter turn) locking system
- Screwless terminals

**IP44** *Splashproof*

A CURRENT	V VOLTAGE	Hz FREQUENCY		EARTH HR POS.		EARTH HR POS.		EARTH HR POS.
			<b>2P+E</b>		<b>3P+E</b>		<b>3P+N+E</b>	
<b>16</b> IP44	<b>110</b>	50-60	31886	4				
	<b>240</b>	50-60	31880	6				
	<b>415</b>	50-60			31881	6	312001	6
<b>32</b> IP44	<b>110</b>	50-60	310085	4				
	<b>240</b>	50-60	31882	6				
	<b>415</b>	50-60			31883	6	312002	6



Amperes	16			32		
	3	4	5	3	4	5
Poles	3	4	5	3	4	5
Ø a	53	58	64	66	66	74
b	142	147	156.5	181	181	181
Ø c	5	5	7	8	8	8.5
Ø d	14.5	15.5	17.5	23.5	23.5	26
e	72	78	85	90	90	99
Conductor mm <sup>2</sup> min	1	1	1	2.5	2.5	2.5
Conductor mm <sup>2</sup> max	2.5	2.5	2.5	6	6	6