

CRIMPER 1600 FERRULES AWG 10-6



Cat No: PA1649 UPC No: 769328100785

Description

- Professional crimping tool for insulated and non-insulated wire ferrules with a wire range of 10-6 AWG (6-16 mm²)
- Fixed steel die system
- Ferrules insert from side of the tool
- Ferrule crimp conforms to DIN standards
- Durable steel construction for long life
- Ergonomic handles for low-effort operation

Specifications

- Application : For Insulated And Non-Insulated Wire Ferrules With A Wire Range Of 10-6 AWG (6.000 - 16.000 SQ-MM)
- Crimping Range : 10-6 AWG
- Handle Type : Ergonomic
- Material : Durable Steel
- Standard : DIN
- Type : Wire Ferrule
- Weight : 15.200 OZ (430.000 GM)