

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [25001-0602](#)  
**Status:** **Active**  
**Overview:** Ribbon Cable Jumpers  
**Description:** 2.54mm Pitch Board-to-Board Ribbon Cable Jumper - 26 AWG, Stranded Topcoat, 6 Circuits, Strip and Retain, 0.051m Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

|                         |                                      |
|-------------------------|--------------------------------------|
| Product Family          | Cable                                |
| Series                  | <a href="#">25001</a>                |
| Crimp Quality Equipment | Yes                                  |
| Geographic Area         | Asia                                 |
| Overview                | <a href="#">Ribbon Cable Jumpers</a> |
| Product Name            | Ribbon                               |
| UPC                     | 800754968546                         |

**Physical**

|                               |                          |
|-------------------------------|--------------------------|
| Cable Length                  | 0.051m                   |
| Circuits (Loaded)             | 6                        |
| Circuits (maximum)            | 6                        |
| Insulation                    | PVC                      |
| Net Weight                    | 1.048/g                  |
| Packaging Type                | Bag                      |
| Pitch - Termination Interface | 2.54mm                   |
| Temperature Range - Operating | -20°C to +105°C          |
| Wire Size AWG                 | 26                       |
| Wire/Cable Type               | (7x34) Stranded, Topcoat |

**Electrical**

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | N/A  |
| Voltage - Maximum             | 300V |

**Material Info**

**Reference - Drawing Numbers**

|               |              |
|---------------|--------------|
| Sales Drawing | SD-25001-001 |
|---------------|--------------|



*image - Reference only*

**EU RoHS**

**ELV and RoHS  
Compliant**  
**REACH SVHC  
Not Reviewed**  
**Low-Halogen Status  
Not Reviewed**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**  
[25001Series](#)