

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0330120003](#)
Status: **Obsolete**
Overview: [mx150 sealed connector system](#)
Description: MX150™ Female Terminal, Tin (Sn) Plating, 22 AWG, Right Reel Payoff, Small Polarization Rib, Contact Material Thickness 0.25mm (.010")

Documents:
[Drawing \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	33012
Application	Power
Comments	Right Reel Payoff, Small Polarization Rib
Crimp Quality Equipment	Yes
Overview	mx150 sealed connector system
Product Name	MX150™

Physical

Gender	Female
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Packaging Type	Reel
Plating min - Mating	0.508µm (20µ")
Plating min - Termination	0.508µm (20µ")
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.60mm (.102") max.
Wire Size AWG	22
Wire Size mm²	0.35, 0.50

Electrical

Current - Maximum per Contact	22A
Voltage - Maximum	250V

Material Info



image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

**Contains SVHC: No
Low-Halogen Status
Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[33012Series](#)

Use With

[33472](#) Dual Row Housing, [33476](#) Hybrid Housing, [33471](#) Single Row Housing