

Product Model : EM-I8270-H

Mold Pictures



System Physical Standard Configuration:

Type	Details	Descriptions
Product Form	Product Form	Straight Plate
	Dimensions	191.6mm*109mm*9.5mm
LCD	Screen Size	7" 10:16
	Screen Resolution	800*1280 IPS
TP	Touch Module	5 Point Capacitive
Battery	Type	Lithium-ion polymer battery
	Capacity	3.7V/3500mAh
	Endurance	4-6 Hours

System hardware configuration:

Type	Details	Descriptions
CPU	Type	Intel Baytrail-T(Quad-core), Z3735G
	Speed	1.33Ghz--1.83GHz
GPU	Type	Intel HD Graphic(Gen7)
RAM	Capacity	1GB DDR3L
ROM Flash	Capacity	16GB
Camera	Front	2.0MP
	Rear	2.0MP
Speaker	Size	Built-in 8Ω/0.8W speaker x 1
G-sensor	Built-in	Gravity acceleration sensor

Network Connections:

Type	Details	Descriptions
WIFI	WIFI module	WIFI 802.11 b/g/n+BT 4.0
3G	External	3G USB dongle
Ethernet Network	MINI USB switch to Ethernet Network	Supportive

Interface Configuration:

Type	Details	Descriptions
Memory card socket	External memory	Support SDHC/SDXC
USB interface	Data transfer supportive	USB OTG
Headphone jack	Music output	φ 3.5mm standard headphone jack
HDMI interface	Video output	Micro HDMI 1.4a
Keyboard	Input device	USB、BT Expunable Wired / Wireless Supportive
Mouse	Input device	USB、BT Expunable Wired / Wireless Supportive

Necessary Accessories:

Type	Details	Descriptions
Power adapter	Standard Configuration	USB (5V/2A)
USB patch cord	Standard Configuration	HOST

Software Configuration:

Type	Details	Descriptions
Operating System	Operating system version	Windows8.1