

Product Model: EM-I8011-S

Mold Pictures



System Physical Standard Configuration:

Type	Details	Descriptions
Product Form	Product Form	Straight Plate
	Dimensions	258*172.6*10.5mm
LCD	Screen Size	10.1' 16:10
	Screen Resolution	1280x800 IPS Screen
TP	Touch Module	10 Point Capacitive
Battery	Type	Lithium-ion polymer battery
	Capacity	3.7V/7900mAh
	Endurance	6-8 Hours

System hardware configuration:

Type	Details	Descriptions
CPU	Type	Intel Baytrail-T(Quad-core), Z3735F
	Speed	1.33Ghz--1.8GHz
GPU	Type	Intel HD Graphic(Gen7)
RAM	Capacity	2GB DDR3L
ROM Flash	Capacity	32GB
Camera	Front	2.0MP
	Rear	2.0MP
Speaker	Size	Built-in 8Ω/0.8W speaker x 2
G-sensor	Built-in	Gravity acceleration sensor

Network Connections:

Type	Details	Descriptions
WIFI	WIFI module	WIFI 802.11 b/g/n+BT 4.0
3G	External	3G USB dongle
Ethernet Network	Mini USB switch to Ethernet Network	Supportive

Interface Configuration:

Type	Details	Descriptions
Memory card socket	External memory	Support SDHC/SDXC
USB interface	Data transfer supportive	HOST USB
Headphone jack	Music output	§ 3.5mm standard headphone jack
DC connector	Power	§ 2.5MM power connector
HDMI interface	Video output	HDMI 1.4a
Keyboard	Input device	Pogo pin connect
Mouse	Input device	USB、BT Expunable Wired / Wireless Supportive

Necessary Accessories:

Type	Details	Descriptions
3.5-inch headphone	Standard Configuration	Standard stereo headphones
Power adapter	Standard Configuration	5V/2A
USB patch cord	Standard Configuration	HOST

Software Configuration:

Type	Details	Descriptions
Operating System	Operating system version	Windows 8.1