



Buyer's Guide | VGA and RGB Cable

	Interface	3-ft. (0.9-m)	5-ft. (1.5-m)	6-ft. (1.8-m)	10-ft. (3.0-m)	15-ft. (4.5-m)	20-ft. (6.0-m)	25-ft. (7.6-m)	35-ft. (10.6-m)	50-ft. (15.2-m)	75-ft. (22.8-m)	100-ft. (30.4-m)	150-ft. (45.7-m)	200-ft. (60.9-m)	Product Name
 HD15  BNC	HD15 to HD15 with Ferrite Core	EVNPS06-0003-FF, -MM, -MF	EVNPS06-0005-FF, -MM, -MF	—	EVNPS06-0010-FF, -MM, -MF	—	EVNPS06-0020-FF, -MM, -MF	EVNPS06-0025-FF, -MM, -MF	—	EVNPS06-0050-FF, -MM, -MF	EVNPS06-0075-FF, -MM, -MF	EVNPS06-0100-FF, -MM, -MF	—	—	VGA Video Cable with Ferrite Core
	HD15 to HD15	EVNPS05-0003-FF, MM, -MF	EVNPS05-0005-FF, MM, -MF	—	EVNPS05-0010-FF, MM, -MF	—	EVNPS05-0020-FF, MM, -MF	EVNPS05-0025-FF, MM, -MF	EVNPS05-0035-FF, MM, -MF	EVNPS05-0050-FF, MM, -MF	EVNPS05-0075-FF, MM, -MF	EVNPS05-0100-FF, MM, -MF	EVNPS05-0150-FF, MM, -MF	EVNPS05-0200-FF, MM, -MF	Premium VGA Extension Cable, PVC, Straight Hoods
	HD15 to HD15	—	EVNPS10-0005-FF, MM, -MF	—	EVNPS10-0010-FF, MM, -MF	—	EVNPS10-0020-FF, MM, -MF	—	—	—	—	—	—	—	Premium VGA Extension Cable, PVC, 90° Hoods
	HD15 M to HD15 M	—	EVNPS08-0005-MM	—	EVNPS08-0010-MM	EVNPS08-0015-MM	—	—	—	—	—	—	—	—	Ultra-Thin SVGA Cable
	HD15 M/3.5-mm to HD15 M/3.5-mm	EVNPS09-0003	EVNPS09-0005	—	EVNPS09-0010	EVNPS09-0015	EVNPS09-0020	EVNPS09-0025	EVNPS09-0035	EVNPS09-0050	EVNPS09-0075	EVNPS09-0100	—	—	Premium VGA Cable with Audio
	(1) HD15 M to (5) BNC M	EYRGBS4-0003	—	EYRGBS4-0006	EYRGBS4-0010	EYRGBS4-0015	EYRGBS4-0020	—	—	—	—	—	—	—	VGA-RGBHV Cable
	(4) BNC M to (4) BNC M	—	—	—	EYNRGBS2-0010-MM	—	—	EYNRGBS2-0025-MM	—	EYNRGBS2-0050-MM	—	—	—	—	RGBS Video Cable
	(4) BNC F to (4) BNC F	—	EYNRGBS2-0005-FF	—	EYNRGBS2-0010-FF	—	—	—	—	—	—	—	—	—	—
	(5) BNC M to (5) BNC M	—	—	EYRGBS5-0006	EYRGBS5-0010	—	EYRGBS5-0020	—	—	—	—	—	—	—	—