

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0039000030**
Status: **Planned for Obsolescence**
Description: 2.00mm (.079") Pitch Board-In Crimp Terminal 5378, 24-28 AWG, PCB Hole Diameter 0.8mm (.031"), Bag

Documents:

[3D Model](#) [Product Specification PS-5379-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	5378
Application	Signal
Comments	PCB Hole Diameter 0.8mm (.031")
Crimp Quality Equipment	Yes
Product Name	Board-In

Physical

Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Packaging Type	Bag
Plating min - Mating	0.889µm (35µ")
Plating min - Termination	0.889µm (35µ")
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.50mm (.059") max.
Wire Size AWG	24, 26, 28
Wire Size mm ²	N/A

Electrical


Current - Maximum per Contact	1.5A, 2A
Voltage - Maximum	125V

Material Info

Old Part Number	5378TL
-----------------	--------

Reference - Drawing Numbers

Product Specification	PS-5379-001, RPS-5379-002
Sales Drawing	SD-5378*



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[5378Series](#)

Use With

[5379 Crimp Housing](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool	0011030044
Hand Crimp Tool for 2.00mm (.079") Pitch Board-In Male Crimp Terminal	0638234800