

Suspended Scales

MECHANICAL



5 kg oblong stainless steel pan
(Can be supplied with 235 6S & 235 10S only)

	Dual marked	
235 6S	5 kg x 20 g/11 lb x 1 oz	
235 10S	5 kg x 10 g/11 lb x 1/2 oz	

5 kg & 10 kg double lipped stainless steel scoop

Can be supplied with 235 10X

	Metric	Dual marked
235 10X	5 kg x 10 g 10 kg x 20 g	5 kg x 10 g/11 lb x 1/2 oz 10 kg x 20 g/22 lb x 1 oz



10 kg & 25 kg round stainless steel pan 305 mm diameter

Can be supplied for retrofitting to the following suspended scales:

	Metric	Dual marked
235 6S	10 kg x 50 g	10 kg x 50 g/22 lb x 2 oz
235 6M	25 kg x 100 g	25 kg x 100 g/55 lb x 4 oz
235 10S	10 kg x 20 g	
235 10X (Non-trade)	10 kg x 20 g 25 kg x 50 g	10 kg x 20 g/22 lb x 1 oz



P.O. Box 9533, Smethwick, West Midlands, B66 2TE
Tel: 0870 444 6132 Fax: 0870 010 2241
E-mail: sales@salterbrecknell.co.uk



Suspended Scales

MECHANICAL



- robust
- accurate
- reliable
- portable
- low cost
- easy to read
- corrosion resistant
- capacities from 5 kg - 300 kg


Suspended Scales

MECHANICAL

Model 235 6S

Compact, robust and corrosion resistant, 150 mm diameter dial housed in a tough ABS plastic case with shatterproof polycarbonate dial cover. Low friction acetal bearings provide positive movement to give maximum sensitivity. Accurate to one part in 250 with up to 15% zero adjustment. Supplied with top and bottom hook.

Option
Oblong pan (5 kg only).



Metric


5 kg x 20 g
10 kg x 50 g
25 kg x 100 g
50 kg x 200 g
100 kg x 500 g

Dual marked

5 kg x 20 g / 11 lb x 1 oz
10 kg x 50 g / 22 lb x 2 oz
25 kg x 100 g / 55 lb x 4 oz
50 kg x 200 g / 110 lb x 8 oz
100 kg x 500 g / 220 lb x 1 lb

Model 235 6M

Compact and robust, 150 mm diameter dial housed in the traditional metal case. Accurate to one part in 250 with up to 15% zero adjustment. Supplied with top and bottom hooks



Metric

5 kg x 20 g
10 kg x 50 g
25 kg x 100 g
50 kg x 200 g
100 kg x 500 g

Dual marked

5 kg x 20 g / 11 lb x 1 oz
10 kg x 50 g / 22 lb x 2 oz
25 kg x 100 g / 55 lb x 4 oz
50 kg x 200 g / 110 lb x 8 oz
100 kg x 500 g / 220 lb x 1 lb


Model 235 10S

Robust and corrosion resistant, large easy to read 254 mm diameter dial housed in a tough ABS plastic case with a shatterproof polycarbonate dial cover. Low friction bearings provide positive movement to give maximum sensitivity. Accurate to one part in 500 with up to 15% zero adjust. Supplied with top and bottom hooks.

Option
Oblong pan (5 kg only).

Metric

5 kg x 10 g
10 kg x 20 g
25 kg x 50 g
50 kg x 100 g
100 kg x 200 g



Model 235 10X (Trade & Non-Trade)

Heavy duty suspended scale, Eu trade approved up to 100 kg. 254 mm diameter easy to read dial housed in a robust grey die cast casing with low friction bearings providing positive movement to give maximum sensitivity. Accurate up to one part in 1000 trade, One part in 500, non-trade. Supplied with top and bottom hooks as standard. Double dial versions available, metric only, or up to 50 kg, dual marked.

Option
Swivel bottom hook.
Double lipped scoop (5 kg/10 kg only)

Metric

5 kg x 10 g
10 kg x 20 g
25 kg x 50 g
50 kg x 100 g
100 kg x 200 g
200 kg x 500 g
300 kg x 1 kg

Dual marked

5 kg x 10 g / 11 lb x 1/2 oz
10 kg x 20 g / 22 lb x 1 oz
25 kg x 50 g / 56 lb x 2 oz
50 kg x 100 g / 110 lb x 4 oz
100 kg x 200 g / 220 lb x 8 oz
200 kg x 500 g / 440 lb x 1 lb
300 kg x 1 kg / 660 lb x 2 lb

