



Einhell

TH-TS 820 Table Saw

Features

- Improved parallel guide (1) with two stop heights
- The saw blade is pivotable from 0° - 45° to the left side (2)
- Cable fixing
- Push stick (4) with handy holder at the machine
- Improved saw blade protection

Technical Data

- Mains: 230 V ~ 50 Hz
- Power: 800 Watt S2 10 min
- No load speed: 2.950 min⁻¹
- Carbide tipped saw blade: Ø 200 x Ø 16 x 2.4 mm
- No. of teeth: 20
- Cutting height max. 90°/ 45°: 43 mm / 35 mm
- Table size: 500 x 335 mm
- Adaptor for dust extraction: Ø 35 mm
- Product weight: 11.5 kg

Logistic Data

- Net weight: 12.1 kg
- Gross weight: 13.6 kg
- Packing dimensions: 525 x 355 x 345 mm
- Bar code: 4006825 590784
- Sales Unit: 1 pc

