

KB235

Keyboard & MOUSE



USB • Standard Keyboard • 4 Button Optical Scroll Mouse



USB CONNECTION

For instant Plug & Play set-up



ANTI-BACTERIAL COATING

Helps prevent the spread of germs, bugs & flu viruses



WATER RESISTANT

Allows liquid to pass through the keyboard preventing damage



LOW NOISE KEYS

For low noise operation ensuring a quiet typing environment



1000/1600dpi
Adjustable Resolution

HIGH RESOLUTION

For accurate & precise movement adjustable via the button above the scroll wheel



SYMMETRICAL DESIGN

Suitable for both left & right handed users



DURABLE DESIGN


Sturdy construction designed to withstand day-to-day wear & tear

KEYBOARD FEATURES

- Entry level keyboard the essential PC accessory suitable for both office and home environments.
- Slim compact design features raising capacity feet allowing the keyboard to be adjusted to the angle you require
- Rubberised pads ensure the keyboard remains in place while in use
- Driverless devices allows instant Plug & Play set-up
- Illuminated Num Lock, Caps Lock and Scroll Lock
- Sturdy construction - designed to withstand day-to-day wear & tear

MOUSE FEATURES

- The essential accessory for any Desktop PC in both office and home environments
- Latest optical technology - works on a variety of surfaces
- No ball or moving parts to collect dust or dirt means less cleaning is required and sticking is eliminated
- A rubberised coating has been added to both the scroll wheel & buttons for none slip use
- Symmetrical design makes this mouse suitable for left & right handed users



COMPUTER GEAR

Essential PC Accessories

KEYBOARD SPECIFICATIONS

- Interface: USB 2.0
- Cable length: 1.5M
- Keys: 105
- LED Indicators: Num, Caps, Scroll lock
- Dimensions: 445 x 25 x 115mm (W x H x D)

SYSTEM COMPATIBILITY

- Windows 2000 & above

TECHNICAL SPECIFICATIONS

- Button life: 10 million cycles (MTBF)
- Working voltage: 3V - 5V
- Working current: <5mA
- Standby current: <5mA
- Sleeping current: <5mA
- Operating temp: 0°C ~ 40°C
- Operating humidity: 20% ~ 90% RH

MOUSE SPECIFICATIONS

- Interface: USB 2.0
- Cable length: 1.2M
- Buttons: 4
- Dimensions: 63 x 35 x 116mm (W x H x D)

SYSTEM COMPATIBILITY

- Windows 2000 & above
- Mac compatible

TECHNICAL SPECIFICATIONS

- Button life: 3 million cycles (MTBF)
- Scroll wheel life: 100,000 cycles (MTBF)
- Sensor report rate: 3500 frames/sec
- Sensor light: Red LED
- Operating temp: 0°C ~ 40°C
- Operating humidity: 20% ~ 90% RH

PACKAGING DETAILS

- Product box dimensions: 550 x 175 x 30mm (W x H x D)
- Primary packaging material: Cardboard
- Primary packaging weight: TBA
- Secondary packaging material: Plastic
- Secondary packaging weight: TBA
- Product and packaging weight: TBA
- Box qty: TBA
- Carton size: TBA
- Total carton weight: TBA
- Country of origin: China

PRODUCT CODE	DETAILS	BOX QTY
24-0235	Black	20

