

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [172677-0200](#)
Status: **Active**
Overview: SolderRight™ Direct-Solder Terminals
Description: SolderRight™ Right-Angle Direct Solder Terminal 26-28 AWG In-Line Mount, Tin

Documents:

[Drawing \(PDF\)](#) [Test Summary TS-172249-001 \(PDF\)](#)
[Product Specification PS-172249-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	172677
Application	Power
Crimp Quality Equipment	Yes
Overview	SolderRight™ Direct-Solder Terminals
Product Name	SolderRight™
UPC	887191934037

Physical

Gender	Male
Material - Metal	Brass
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Net Weight	0.038/g
Packaging Type	Reel
Plating min - Mating	1.524µm
Plating min - Termination	1.524µm
Termination Interface: Style	Through Hole
Wire Insulation Diameter	1.20-1.30mm
Wire Size AWG	26, 28
Wire Size mm²	0.09-0.13

Electrical

Current - Maximum per Contact	4.2A
-------------------------------	------

Material Info

Reference - Drawing Numbers

Product Specification	PS-172249-001
Sales Drawing	SD-172677-001
Test Summary	TS-172249-001




image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

**Contains SVHC: No
Low-Halogen Status
Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

[172677Series](#)

Mates With

Solder straight to PCB

Application Tooling | [FAQ](#)

*Tooling specifications and manuals are
 found by selecting the products below.
 Crimp Height Specifications are then
 contained in the Application Tooling
 Specification document.*

Global

Description	Product #
Hand Crimp Tool for SolderRight™ Board-In Terminals	0638273300