

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19160-0009](#)
Status: **Active**
Overview: [Splices](#)
Description: Closed-End Insulated Splice for 12-22 AWG Wire

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-19408-109 \(PDF\)](#)
[Product Specification PS-19902-013 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Splices
 Series [19160](#)
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 MolexKits Yes
 Overview [Splices](#)
 Product Name Closed-End Insulated
 UPC 800753110182

Physical

Barrel Type Closed
 Color - Resin Natural
 Flammability 94V-2
 Insulation Nylon (PA)
 Material - Metal Copper
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 0.689/g
 Packaging Type Bag
 Temperature Range - Operating 105°C
 Wire Insulation Diameter 6.86mm max.
 Wire Size AWG 12, 14, 16, 18, 20, 22

Electrical

Voltage - Maximum 600V

Material Info

Old Part Number NC-2212

Reference - Drawing Numbers

[Packaging Specification](#) PK-19408-109
[Product Specification](#) PS-19902-013
[Sales Drawing](#) SD-19160-001




image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

**Contains SVHC: No
Low-Halogen Status
Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19160Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool	0640010900
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050900
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640053600