

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [15-97-9121](#)  
**Status:** **Active**  
**Overview:** Mini-Fit® TPA Plugs and Receptacles  
**Description:** Mini-Fit® TPA Key for 12 Circuit

**Documents:**

[3D Model](#) [Packaging Specification PK-30072-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-5556-003 \(PDF\)](#)

**General**

Product Family	Crimp Housings
Series	<a href="#">30072</a>
Application	Power, Wire-to-Board, Wire-to-Wire
Overview	<a href="#">Mini-Fit® TPA Plugs and Receptacles</a>
Product Name	Mini-Fit® TPA
UPC	800754203104

**Physical**

Circuits (maximum)	12
Color - Resin	Natural
Gender	Female
Glow-Wire Compliant	No
Material - Resin	Nylon
Net Weight	0.256/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Stackable	No
Temperature Range - Operating	-40°C to +105°C

**Electrical**

Current - Maximum per Contact	13A
-------------------------------	-----

**Material Info**

Old Part Number	30072-12
-----------------	----------

**Reference - Drawing Numbers**

Packaging Specification	PK-30072-001
Product Specification	PS-5556-003
Sales Drawing	SD-30072-*



**EU RoHS**

**ELV and RoHS  
Compliant**

**REACH SVHC  
Contains SVHC: No  
Low-Halogen Status  
Low-Halogen**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of  
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

**Search Parts in this Series**

[30072Series](#)

**Mates With**

[30068](#) , [30069](#) , [30069](#) , [30070](#) , [30070](#) ,  
[44473](#)

**Use With**

[30067](#) 4.20mm Pitch Mini-Fit® Crimp  
 Housing