



iMedia[®] Interactive[™] HD2

1080P HIGH-DEFINITION DIGITAL SIGNAGE DISPLAY GENERATOR
Model: AV25047



- Introduction**
About AEI
- DigiSender**
Video Senders
- DigiSenderTV**
SuperSmartTV Upgrades
- iMedia**
Android Devices
- AEI Security**
Alarm Systems & CCTV
- Remote Automation**
Gadgets for the Home

- iMedia Blaze**
Tablets
- iMedia Atom**
Smartphones
- iMedia Eclipse**
Netbooks
- iMedia Gamer**
Consoles & Gamepads
- iMedia Interactive**
Digital Signage
- Accessories

- Interactive 4K**
DGIMI4KB2
- Interactive HD**
DGIMIHD1
- Interactive HD2**
DGIMIHD2
- Interactive HD Mini**
DGIMIHD1A1
- Display Projector**
DGIMIPHD
- Display Touch Film**
DGIMITF

- AEI Security & Communications Ltd.**
Weslake Industrial Park,
Rye Harbour Road, Rye,
East Sussex, TN31 7TE
Web:
www.digisender.net
Email:
sales@aei.eu
Telephone:
02071 931 413



The iMedia Interactive HD is a robust high definition digital signage display generator. It features a tremendously straightforward interface designed and built in the UK for consumers and engineers alike. It includes all the connectivity you need such as HDMI out, Wifi, USB and Ethernet.

It is a remote digital signage management console and allows you to create an on-board digital signage which can integrate with Internet based web pages with Live Streaming TV and news feeds. Because the console is built around on-board fast hardware codec management it means that you can create signage remotely and utilize live video steaming content from the internet. It connects to a flat screen display via HDMI ver 1.4 and presents a display from a choice of interfaces that forms part of the user interface. The web page service is a full screen facility where you control the HTML page on your own server (or a clients server) and display the URL in full screen. It includes a selection of templates which include live video, XML news feeds, Google maps with congestion or points of interst, youtube video player, music background player and lots more. For full details please visit <http://www.imediasignage.com> for video guides on how to get up.

Features

- HDMI Out v1.4 (1920 x 1080 max.)
- HDMI, Signage or Internet TV Source selection
- Image rotation with 90/180/270 degree or XY
- Back-up Remote Management via Windows RTP
- Secure HTTP connection & Dynamic IP remote login facility
- Display Scheduling
- Displays Images, XML Feeds and HTML web sites.
- Set up a digital Display in seconds with a built in interface.
- HTML 5 + Flash Player + Web Audio API
- Make screen presentations from your mobile via Miracast
- Create an auto-pairing Bluetooth 4.0 connection via NFC
- UI + FW OTA Auto update

Specifications

- Operating System: Android 4.2.2
- Processor: 1.5GHz Dual-Core ARM Cortex-A9
- Graphics: Dual-Core ARM Mali-400
- Memory: 1GB DDR3 SDRAM
- Internal Storage: 4GB NAND Flash
- External Storage: Up to 32GB via Micro SD (not supplied) & up to 2TB via USB HDD (not supplied)
- Network: WiFi: 802.11 b/g/n, LAN (10/100/1000Mbps), Miracast/Wireless Display, DLNA
- I/O: 1x HDMI1.4 output, 1x 3.5mm AV output, 1x Ethernet, 1x USB2.0 OTG, 1x USB2.0 Host, 1x Micro SD Card
- Power: DC 12V 1.5A

Kit Contents

- 1x AV25047 Digital Signage Generator
- 1x AV Cable
- 1x Ethernet Cable
- 1x Power Supply
- 1x Quick Guide