



00104932 "EWS-380" Electronic Weather Station, black/silver

- For digital meteorological observation, with a radio clock
- The barometer shows the atmospheric pressure, thus allowing you to accurately monitor changes in the weather
- DCF radio clock which automatically adjusts to the world's most accurate clock
- Two-part set consisting of a base station and a wireless outdoor sensor (433 MHz) for digital meteorological observation and to display the time, weekday and date
- Allows up to three wireless outdoor sensors to be connected
- Can be wall-mounted or left freestanding

Thermometer:

- Measures the temperature in both degrees Celsius or Fahrenheit
- Stores maximum/minimum values for temperature

Barometer:

- Trend display for atmospheric pressure: rising, settled, falling
- Weather forecast: sunny, slightly cloudy, cloudy, rainy, stormy

Hygrometer:

- Trend display for air humidity

Clock/calendar/alarm function:

- Shows the time in twelve hour or twenty-four hour clock
- Date and weekday display
- Weekday display (7 languages: German, English, Spanish, Italian, French, Swedish, Dutch)
- Alarm function

Technical Details:

- Alarm Function: Yes
- Colour Display: No
- DCF Radio Clock: Yes
- Data Memory: Yes
- Humidity (inside): 25% - 99%
- Humidity (outside): 25% - 99 %
- Hygrometer: Yes
- Measurement Range (inside): -20°C to +60°C
- Measurement Range (outside): -20°C to +60°C
- Outdoor Sensor: Yes
- Thermometer: Yes
- Weather Forecast: Yes
- Width x Depth x Height: 8,7 x 2,7 x 18,3
- Number of Batteries (Outdoor Sensor): 2
- Number of Batteries (Station): 2
- Type of Battery (Station): AA Mignon
- Type of Battery Outside Sensor: AA Mignon
- Range to Radio Outdoor Sensor: 30 m
- Colour: Black/Silver

Scope Of Delivery:

- 1 base station
- 1 wireless outdoor sensor
- 4 Mignon batteries
- Operating instructions



