


M24308/2-2F

ITT Cannon - D-Sub Connector

DAMAM15SA101



PRODUCT INFORMATION

Specification:	MIL-DTL-24308
Shielding:	Yes
Connector Type:	Rectangular
Connector Style:	Receptacle
Mounting Type:	Cable or Box - Front Mount - Thru Holes
Contacts, # of:	15
Contact Style:	Socket
Termination Method:	Crimp
Crimp Wire Gauge:	24,22,20
Insert Arrangement:	15
Contact Size:	15#20
Contacts Supplied:	Yes
Contact Material:	Copper Alloy
Contact Plating:	50 microinches Gold Plate
Shell Material:	Steel per ASTM A-620
Shell Plating:	Yellow Chromate over Cadmium
Shell Color:	Yellow
Insert Material:	Thermoplastic UL94VO
Amperage Rating:	7.5A
Operating Voltage AC V RMS Max:	300
Operating Temperature °F (°C):	-67 to +257 (-55 to +125)
Contact Mating Life:	500