

**Technical Characteristics**

Horsepower Rating (3-Phase)	2HP@200VAC - 3HP@230VAC - 5HP@460/575VAC
Inductive Amperes (AC3)	9A
Resistive Amperes (AC1)	20A
Approvals	UL Listed File E164862 NLDX2 - CSA Certified File LR43364 Class 3211 04 - IEC Rated 60947 - CE Marked
Auxiliary Contacts	None
Horsepower Rating (1-Phase)	0.5HP@115VAC - 1.5HP@230VAC
Marketing Trade Name	TeSys
Maximum Voltage Rating	600VAC
Number of Poles	4-Pole
Coil Voltage	110VAC
Mounting Type	Panel
Contactor Type	Non-Reversing
Type	TeSys K
Terminal Type	Screw Clamp
Depth	2.24 Inches
Height	2.28 Inches
Width	1.77 Inches
Weight	0.46 Pounds

**Shipping and Ordering**

Category	22326 - Contactors, AC, Open, Non-Reversing, K-Line
GTIN	00785901641735
Package Quantity	1
Weight	0.4 lbs.
Country of Origin	FR

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.