

Flip-Flop Relay Module

MCM Part #: 28-5115 | Cebek Part #: I-9



Flip-Flop Relay Module

With momentary contact at the input, the output relay closes and latches. Upon a second momentary closure of the same input, the relay opens. Relay contacts 5A.

Product Description

Features

- Requires 12VDC/60mA power supply (not included)
- Operating LED
- Size: 61 x 40 x 30mm / 2.40" x 1.57" x 1.18"

Specifications

Voltage	12 VDC
Minimum consumption	10 mA
Maximum consumption	60 mA
Maximum Temperature	60 ° C
Maximum output load by relay	5A
Impulses Input	Square power frequency free
Protection Against Polarity Inversion	Yes
Operating LED	Yes