



Trolleys

Multi trolleys

Multi trolleys provide an ergonomic mobile workstation. Multi trolleys are available in three different widths: M20, M30 and M36. This means that all our module-sized accessories can be used with the trolleys. Multi trolleys are equipped with four swivel casters (ø 3.93 inches), two of which have brakes. ESD versions are also available.



Multi trolley 1



Multi trolley 2

• = In stock products

name	trolley width		
	M20	M30	M36
Multi trolley 1	C72141001	C72141002 •	C72141003 •
Multi trolley 1 ESD	C72135001	C72135002 •	C72135003 •
Multi trolley 2	C72241001	C72241002 •	C72241003 •
Multi trolley 2 ESD	C72235001	C72235002 •	C72235003 •

Multi trolley frame

name	module	size W x D x H inches	max lbs	order No	ESD order No
Multi trolley 1 frame	M20	20.86 x 28.14 x 44.48	660	860812-41	860812-35
Multi trolley 2 frame	M20	20.86 x 28.14 x 64.17	660	860818-41	860818-35
Multi trolley 1 frame	M30	30.70 x 28.14 x 44.48	660	860154-41 •	860154-35 •
Multi trolley 2 frame	M30	30.70 x 28.14 x 64.17	660	860156-41 •	860156-35 •
Multi trolley 1 frame	M36	36.81 x 28.14 x 44.48	660	860155-41 •	860155-35 •
Multi trolley 2 frame	M36	36.81 x 28.14 x 64.17	660	860157-41 •	860157-35 •

Bottom shelf

name	module	size W x D inches	max lbs	order No	ESD order No
Bottom shelf*	M20	18.50 x 19.88	220	860846-41	860846-35
Bottom shelf	M20	18.50 x 25.59	220	860847-41	860847-35
Bottom shelf*	M30	28.34 x 19.88	220	860057-41 •	860057-35 •
Bottom shelf	M30	28.34 x 25.59	220	860067-41 •	860067-35 •
Bottom shelf*	M36	34.25 x 19.88	220	860059-41 •	860059-35 •
Bottom shelf	M36	34.25 x 25.59	220	860069-41 •	860069-35 •

*Compatible only with Multi trolley 1.

Adjustable shelves are equipped with an ESD mat (35) or non ESD with grooved rubber mat (41).

Front justified adjustable shelf

name	module	size W x D inches	max lbs	order No	ESD order No
Adjustable shelf	M20	18.50 x 19.88	220	92141001	92135001
Adjustable shelf	M20	18.50 x 25.59	220	92141002	92135002
Adjustable shelf	M30	28.34 x 19.88	220	92141005 •	92135005 •
Adjustable shelf	M30	28.34 x 25.59	220	92141006 •	92135006 •
Adjustable shelf	M36	34.25 x 19.88	220	92141009 •	92135009 •
Adjustable shelf	M36	34.25 x 25.59	220	92141010 •	92135010 •

Adjustable shelves are equipped with an ESD mat (35) or non ESD grooved rubber mat (41). May also be used on workstation upright modules. Rear justified adjustable shelves can be found on page 35.

Front justified adjustable shelf, stepless depth adjustment


name	mod	size W x D	max lbs	order No	ESD order No
Adjustable shelf, stepless depth adjust	M20	18.50 x 19.88	110	92141003	92135003
Adjustable shelf, stepless depth adjust	M20	18.50 x 25.59	110	92141004	92135004
Adjustable shelf, stepless depth adjust	M30	28.34 x 19.88	110	92141007	92135007
Adjustable shelf, stepless depth adjust	M30	28.34 x 25.59	110	92141008	92135008
Adjustable shelf, stepless depth adjust	M36	34.25 x 19.88	110	92141011	92135011
Adjustable shelf, stepless depth adjust	M36	34.25 x 25.59	110	92141012	92135012

Adjustable shelves are equipped with an ESD mat (35) or non ESD grooved rubber mat (41). May also be used on workstation upright modules. Rear justified adjustable shelves can be found on page 35.

Module size

The module (M) size refers to the distance between two upright tubes from the middle of the tube.

The module size is used to find the appropriate accessories.



Additional specification details available on page 122.