

# Product data sheet

## Characteristics

# H361A

## SWITCH FUSIBLE HD 600V 30A 3P NEMA12K

Product availability: Stock - Normally stocked in distribution facility



### Main

|                           |   |
|---------------------------|---|
| Commercial Status         | Commercialised                            |
| Product or component type | Single Throw Safety Switch                |
| Line Rated Current        | 30 A                                      |
| Product certifications    | UL listed                                 |
| NEMA degree of protection | NEMA 12 galvanized steel                  |
| Device composition        | None                                      |
| Disconnecter device type  | Fusible disconnect                        |
| Short-circuit current     | 200 kA R, J or L<br>10 kA H or K          |
| Device mounting           | Surface                                   |
| Number of poles           | 3   |
| Electrical connection     | Lugs                                      |
| Series name               | Heavy duty                                |
| System Voltage            | 600 V AC/DC                               |
| AWG gauge                 | 14...6 AWG copper<br>12...6 AWG aluminium |

### Ordering and shipping details

|                       |   |
|-----------------------|---|
| Category              | 00114 - H&HU SW,2&3P,N12K,30-200A                 |
| Discount Schedule     | DE1   |
| GTIN                  | 00785901481850                                    |
| Nbr. of units in pkg. | 1   |
| Package weight(Lbs)   | 10.57   |
| Product availability  | Stock - Normally stocked in distribution facility |
| Returnability         | Y   |
| Country of origin     | US  |

### Offer Sustainability

|                          |   |
|--------------------------|---|
| Sustainable offer status | Not Green Premium product                         |
| RoHS (date code: YYWW)   | Will be Compliant on 3Q2014                       |
| REACH                    | Reference not containing SVHC above the threshold |

### Contractual warranty

|        |           |
|--------|-----------|
| Period | 18 months |
|--------|-----------|

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.