

Product data sheet

Characteristics

DTU361RB

SW NOT FUSIBLE DT 600VAC 30A 3P NEMA3R

Product availability: Stock - Normally stocked in distribution facility



Main

Commercial Status	Commercialised
Product or component type	Double Throw Safety Switch
[In] rated current	30 A
Product certifications	UL listed
NEMA degree of protection	NEMA 3R galvanized steel
Device composition	None
Disconnecter device type	Non-fusible disconnect
Device mounting	Surface
Number of poles	3
[Ue] rated operational voltage	600 V DC 600 V AC
AWG gauge	14...2 AWG copper 12...2 AWG aluminium

Ordering and shipping details

Category	00133 - DT SWITCH,NEMA3R
Discount Schedule	DE1
GTIN	00785901308751
Nbr. of units in pkg.	1
Package weight(Lbs)	37.00
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	US

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Will be Compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Period	18 months
--------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. *Prices are indicative