

Automotive 20A Current Tester

Check up to 20A without breaking the circuit



- Mini-blade connectors plug into the fuse block
- Measuring range: 20A/48VDC (10 seconds max)
- 10mA resolution
- 1.6ft (50cm) connector cable
- $\pm(2\% + 2 \text{ digits})$ accuracy
- 3.4 x 1.5 x 1.1" (86 x 37x 28.5mm) ; 0.15lbs (68g)
- Includes one 12V A23G battery

AUT20M Automotive 20A Current Tester with Mini Fuse

AUT20 Automotive 20A Current Tester with ATC Fuse

Automotive Relay Tester

Quick go/no-go tester provides general health and functioning of common 4 and 5-pin automotive relays

- Pass/Fail dual color LED (green and red)
- 3 relay input configuration sockets (exposed pins only)
- Tests for: Coil resistance, Surge Suppression Device (resistor or diode), Open/closed contact integrity (10 cycles), Contact cyclic testing for intermittent failure detection, Loaded contact continuity, Relay contacts stuck open or closed, Time to contact closure and opening
- Coil Resistance 20 to 500 ohms
- Coil Test Voltage: 9 Volts
- Coil Resistance Threshold: 200 milliohms
- No batteries required — alligator clips with 4.2ft (1.3m) test leads connect to car battery for power
- 5 x 2.7 x 1.2" (128 x 68 x 30mm); 0.4lbs (185g)



AUT100 Automotive Relay Tester

Automotive 30A Current Tester

Check up to 30A without breaking the circuit



- Mini-blade connectors plug into the fuse block
- Measuring range: 30A/48VDC (10 seconds max)
- 10mA resolution
- 2.3ft (71cm) connector cable
- $\pm(2\% + 2 \text{ digits})$ accuracy
- 3.4 x 1.5 x 1.1" (86 x 37x 28.5mm) ; 0.15lbs (68g)
- Includes one 12V A23G battery

AUT30M Automotive 30A Current Tester with Mini Fuse

AUT30 Automotive 30A Current Tester with ATC Fuse

Automotive 80A Current Tester

Check up to 80A without breaking the circuit

- Mini, ATC, and Max blade connectors with 3.9ft (1.2m) cable plug into the fuse block
- Measuring range: 80A/48VDC (10 seconds max)
- 0.1A resolution
- $\pm(2\% + 4 \text{ digits})$ accuracy
- 3.5 digit LCD with bargraph
- Data Hold and Zero function
- 4.4 x 1.8 x 1.3" (112 x 45 x 33mm); 0.4lbs (165g)
- Includes one 9V battery



AUT80 Automotive 80A Current Tester

Automotive Multimeter

14 functions including RPM, Dwell Angle, Duty Cycle and Pulse Width

- RPM measurement using the inductive pickup
- Duty cycle, pulse width and dwell angle measurement
- 4000 count backlit LCD
- Fused current inputs and overload protection on all ranges
- Data Hold, Relative, and 20A Max Current
- Includes one 9V battery



AUT500 Automotive Multimeter

Automotive 30A Current Tester

Check up to 30A without breaking the circuit

- Mini and ATC blade connectors with 1.3ft (40cm) cable plug into the fuse block
- Alligator Clip connectors with 2.5ft (75cm) cable included
- Measuring range: 30A/48VDC (10 seconds max)
- 100mA resolution
- $\pm(2\% + 2 \text{ digits})$ accuracy
- 3.5 digit LCD with bargraph
- Data Hold and Zero function
- 3.4 x 1.5 x 1.1" (86 x 37x 28.5mm); 0.15lbs (68g)
- Includes one 9V battery



AUT35 Automotive 30A Current Tester

Digital Tire Pressure Gauge

More accurate than conventional air gauges

- 5 to 100 PSI
35 to 680 KPa
0.4 to 6.8 Bar
- $\pm(1\% + 1\text{PSI})$ accuracy
- Illuminated white LED tip helps locate the valve stem easier
- 3-1/2 digit backlit LCD
- Auto power off
- 6.1 x 1.7 x 0.8" (156 x 42 x 20mm); 0.2lbs (77g)
- Includes two 1.5V AAA batteries



AUT10 Digital Tire Pressure Gauge

Car Fuse Adapter Test Leads

Use your multimeter to check automotive current up to 20A without breaking the circuit

- Mini or ATC-blade connectors plug into the fuse block
- Measuring range: 20A/48VDC (10 sec max)
- 2.6ft (80cm) connector cable with standard shrouded right-angle banana plugs for use with virtually any DMM with a 20A current input
- $\pm 2\%$ accuracy



AUT-TLM Automotive Mini Fuse Adapter

AUT-TL Automotive ATC Fuse Adapter