


Mini IR Thermometer

✓ Compact thermometer measures up to 500°F (260°C)
 With built-in laser pointer that identifies target area and improves aim

Features:

- Backlighting illuminates display for taking measurements at night or in areas with low background light levels
- Automatic Data Hold when trigger released
- Fixed 0.95 emissivity covers 90% of surface applications
- MAX/MIN
- Auto power off
- Complete with 9V battery and carrying case



Ideal for automotive applications



Test for temperature in heating systems



Checking for heat loss around windows and doors



Specifications	
Range	-4 to 500°F (-20 to 260°C)
Basic Accuracy	±3% of reading or ±5°F/2.5°C (whichever is greater)
Max. Resolution	0.1°F/°C
Emissivity	0.95 fixed
Field of View (Distance to Target)	6:1
Dimensions	3.2 x 1.3 x 5.4" (82x32x137mm)
Weight	4.4oz (125g)

Ordering Information:

IR250Mini IR Thermometer

