

2 Port USB VGA Cable KVM Switch - USB Powered with Remote Switch

StarTech ID: SV211USB



The SV211USB 2-Port VGA Cable KVM Switch lets you control two VGA, USB-equipped PCs with a single monitor, keyboard and mouse.

To help organize your desk without sacrificing valuable work space, this VGA USB KVM switch features a compact footprint and integrated KVM cables that can be connected directly to your systems. Plus, the KVM is USB-powered, eliminating the need for a bulky external power adapter and wall outlet.

This VGA KVM switch offers support for resolutions up to 2048x1536, for the ability to drive a high-resolution VGA display. For simple switching between connected systems, the KVM features a convenient push-button remote switch on a 1.5 meter (5ft) cable, as well as keyboard hot-key support and PC or Mac® compatible switching software.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Great for PC test/burn-in computer control, saving the desk space required for two monitors, keyboards and mice
- Perfect for sharing computers and attached peripherals in the home or home office
- Dual system control for single user workstations, increasing user productivity in the office

Features

- Supports resolutions up to 2048x1536
- Switch PCs via push-button, hot-keys or switching software (included)
- Space-saving design, minimal footprint
- Integrated KVM cables and remote switch
- Switching software supports PC and Mac® platforms
- USB Powered - No external power adapter required
- Supports hot-plugging
- Remote switch on 1.5m (5ft.) cable

Technical Specifications

Warranty	2 Years
Audio	No
KVM Ports	2
PC Interface	USB
PC Video Type	VGA
Multi-Monitor	No
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No
Console Interface(s)	1 - VGA (15 pin; High Density D-Sub) Female
Console Interface(s)	2 - USB A (4 pin) Female
Host Connectors	1 - VGA (15 pin; High Density D-Sub) Male
Host Connectors	1 - USB A (4 pin) Male
IP Control	No
Port Selection Support	Push Button, Hotkeys, and Software
OS Compatibility	Windows® 8 / 8.1 (32/64bit), 7 (32/64), Vista(32/64), XP(32/64), 2000 Windows Server® 2012, 2008 R2, 2003(32/64) Mac OS 10.x (Tested up to 10.9), 9.x
Note	OS Compatibility refers to KVM software only - the KVM itself can be used without software on any platform
Color	Black
Enclosure Type	Plastic
Cable Length	850 mm [33.5 in]
Product Length	88 mm [3.5 in]
Product Width	66 mm [2.6 in]
Product Height	23 mm [0.9 in]
Product Weight	380 g [13.4 oz]
LED Indicators	1 - PC Selection indicator
Power Source	USB-Powered
Operating Temperature	0°C to 40°C (32°F to 104°F)
Storage Temperature	-20°C to 60°C (4°F to 140°F)
Humidity	0~90% RH Non-Condensing
Shipping (Package) Weight	442 g [15.6 oz]
Included in Package	1 - KVM Switch

- Included in Package 1 - Software CD
- Included in Package 1 - Instruction Manual

Certifications, Reports and Compatibility

