

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [02-09-2105](#)
Status: **Active**
Description: Board-In Crimp Terminal, Series 4706, Male, Tin (Sn) Plated Brass Contact, 16-18 AWG, 11.20mm Terminal Progression

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-4706-001 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	4706
Application	Signal
Comments	Progression 11.20mm
Crimp Quality Equipment	Yes
Product Name	Board-In Stand Alone Terminal
UPC	800753615403

Physical

Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.085/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	3.05mm max.
Wire Size AWG	16, 18
Wire Size mm ²	N/A

Material Info

Old Part Number 4706-(P909)

Reference - Drawing Numbers

Product Specification PS-4706-001
 Sales Drawing SD-4706




image - Reference only

EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

4706Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for Board-In Terminal, 16-18 AWG	0011010065
Mini-Mac™ Applicator for Board-In Crimp Terminals	0638934200
Terminator Die	0011402042
Terminator Die - Overlap Insulation Crimp	0011402044

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION