

## RJ45 socket insert - VS-08-BU-RJ45-6/LV-1 - 1653090


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



RJ45 socket insert, for PCB assembly, CAT6, 8-pos., shielded, with straight solder pins, 1x



### Key commercial data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 017918 970048
Weight per Piece (excluding packing)	7.12 g
Custom tariff number	85366990
Country of origin	Japan
Product key	ABNAAD
Note	Made to Order (non-returnable)

### Technical data

#### Mechanical characteristics

Number of positions	8
Number of slots	1
Connection profile	RJ45 8(8)
Shielded	Yes
Insertion/withdrawal cycles	≥ 750
Connection method	Solder connection

#### Ambient conditions

Ambient temperature (operation)	-25 °C ... 80 °C
Degree of protection	IP20

#### Material data

Inflammability class according to UL 94	V0
Housing material	Copper alloy
Contact carrier material	PBT

# RJ45 socket insert - VS-08-BU-RJ45-6/LV-1 - 1653090

## Technical data

### Material data

Contact material	Copper alloy
Contact surface material	Gold over nickel

### Electrical characteristics

Number of positions	8
Transmission characteristics (category)	CAT6
Rated current	1 A
Pollution degree	1

## Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260705
eCl@ss 7.0	27440309
eCl@ss 8.0	27440309

### ETIM

ETIM 2.0	EC000438
ETIM 3.0	EC000438
ETIM 4.0	EC000438
ETIM 5.0	EC000438

### UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

## Approvals

### Approvals

---

Approvals

GOST

---

Ex Approvals

## RJ45 socket insert - VS-08-BU-RJ45-6/LV-1 - 1653090

### Approvals

---

Approvals submitted

---

### Approval details



### Accessories

#### Accessories

#### Panel mounting frame

Panel mounting frames - VS-08-A-RJ45/LP-1-IP 20 - 1688641



RJ45 panel mounting frame, 1x, IP20, for PCB assembly, for socket inserts, without mounting screws

---

Panel mounting frames - VS-PPC-F1-RJ45-MNNA-1R-PHA - 1608029



RJ45 panel mounting frame, IP67, for push-pull interlocking, metal, for PCB connection, for square panel cutout, with grommet, without mounting screws

---

Panel mounting frames - VS-PPC-F1-RJ45-P0BK-1R-PHA - 1657847




RJ45 panel mounting frame, IP67, for push-pull interlocking, plastic, for PCB connection, for square panel cutout, with grommet, without mounting screws

---


### Drawings

# RJ45 socket insert - VS-08-BU-RJ45-6/LV-1 - 1653090

Schematic diagram




Drilling diagram



Drilling diagram

Dimensioned drawing



RJ45 socket insert