

RJ45 coupling - VS-08-KU-IP67 - 1689268

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




RJ45 coupling, IP67, CAT5e, with protective cover, color: gray



Ethernet

Key commercial data

Packing unit	1 pc
GTIN	 4 017918 938185
Weight per Piece (excluding packing)	44.94 g
Custom tariff number	85366990
Country of origin	Germany
Product key	ABNACF

Technical data

Mechanical characteristics

Number of positions	8
Connection profile	RJ45 8(8)
Insertion/withdrawal cycles	≥ 750
Connection method	Coupling
Cable exit	Straight
Color	gray

Ambient conditions

Ambient temperature (operation)	-10 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Degree of protection	IP67

Material data

Inflammability class according to UL 94	V0
Housing material	PBT
Contact carrier material	Thermoplastic
Contact material	Copper alloy

RJ45 coupling - VS-08-KU-IP67 - 1689268

Technical data

Material data

Contact surface material	Gold over nickel
Sealing material	NBR
Seal material	NBR

Electrical characteristics

Number of positions	8
Transmission characteristics (category)	CAT5 (IEC 11801:2002), CAT5e (TIA 568B:2001)
Rated current	1 A
Surge voltage category	I
Pollution degree	1

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27261203
eCl@ss 7.0	27440202
eCl@ss 8.0	27440202

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / cULus Recognized

RJ45 coupling - VS-08-KU-IP67 - 1689268

Approvals

Ex Approvals

Approvals submitted

Approval details

UL Recognized	
Nominal current IN	1.75 A
Nominal voltage UN	50 V

cUL Recognized	
Nominal current IN	1.75 A
Nominal voltage UN	50 V

cULus Recognized	
------------------	--

Accessories

Accessories

Protective cover

Protective covers - VS-08-SD-F - 1652606


Protective cover, IP67, flat design, to cover the contact insert in the panel mounting frame, color: gray



Drawings

RJ45 coupling - VS-08-KU-IP67 - 1689268

Dimensioned drawing



RJ45 coupling

Phoenix Contact 2014 © - all rights reserved
<http://www.phoenixcontact.com>