

Economy Rack Chassis *RMC Series*

Features



- Uses all machine screw & PEM nut construction, perfect for applications where repetitive assembly and disassembly are required.
- Light weight design - all aluminum, type 5050 H32 for easy modification. Example: the 19" rack mountable enclosure (RMCS190313BK1) shown in the left photo above - weighs only 5 pounds (2.3 Kg).
- Strong design construction using:
 - 0.125" (3.2 mm) thick - side panels & rack mount brackets
 - 0.064" (1.6 mm) thick - front & rear panels
 - 0.062" (1.6 mm) thick - top and bottom panels
- Can be used with or without rack mounting "ears" or brackets (included).
- Enclosure is finished in rugged, satin texture, black powder paint
- Includes top, bottom, side panels, front & rear panels, rubber self adhesive feet, rack mount brackets and all hardware
- Link below for more information on our chrome pull handles (not included with unit)
- Easy access to inside, only 4 screws need to be removed from any of the 6 panels for internal access.
- Internal aluminum chassis panel is optional (see below).
- Knockdown design ships unassembled for easy handling and shipping protection.
- Note: Grounding options available through our modification process. Panels are not grounded to frame due to powder coat finish.
- RoHS Compliant.
- Manufactured in North America.

Gallery



Accessories

Chassis Handles

Mounting Hardware

Part No. Solid Top/Bottom	Part No. Vented Top/Bottom	Overall Dimensions			Usable Mounting Dimensions		Inside Height	Accepts
		Height	Width	Depth	Rack Units	Height	Clearance With Chassis Installed	Pull Handle Part No.
RMCS9018BK1	RMCV9018BK1	1.73	8.50	8.00	1U	1.75	0.81	-
RMCS19018BK1	RMCV19018BK1	1.73	17.00	8.00	1U	1.75	0.81	-
RMCS190113BK1	RMCV190113BK1	1.73	17.00	13.00	1U	1.75	0.81	-
RMCS9038BK1	RMCV9038BK1	3.48	8.50	8.00	2U	3.50	2.56	1427P
RMCS19038BK1	RMCV19038BK1	3.48	17.00	8.00	2U	3.50	2.56	1427P
RMCS190313BK1	RMCV190313BK1	3.48	17.00	13.00	2U	3.50	2.56	1427P
RMCS9058BK1	RMCV9058BK1	5.23	8.50	8.00	3U	5.25	4.31	1427N
RMCS190513BK1	RMCV190513BK1	5.23	17.00	13.00	3U	5.25	4.31	1427N
RMCS190713BK1	RMCV190713BK1	6.98	17.00	13.00	4U	7.00	6.06	1427M
RMCS190813BK1	RMCV190813BK1	8.73	17.00	13.00	5U	8.75	7.81	1427M
RMCS191013BK1	RMCV191013BK1	10.48	17.00	13.00	6U	10.50	9.56	1427L
RMCS191015BK1	RMCV191015BK1	10.48	17.00	15.00	6U	10.50	9.56	1427L

Front & Rear Replacement Panels (Full 17" Width Only)

Part No. Textured Black	Part No. Smooth Black	Part No. Beige	Mounting Dimensions	
			Height	Rack Units
RMCP1	RMCP1BK	RMCP1CG	1.75	1U
RMCP1	RMCP1BK	RMCP1CG	1.75	1U
RMCP3	RMCP3BK	RMCP3CG	3.5	2U
RMCP3	RMCP3BK	RMCP3CG	3.5	2U
RMCP5	RMCP5BK	RMCP5CG	5.25	3U
RMCP7	RMCP7BK	RMCP7CG	7	4U
RMCP8	RMCP8BK	RMCP8CG	8.75	5U
RMCP10	RMCP10BK	RMCP10CG	10.5	6U
RMCP10	RMCP10BK	RMCP10CG	10.5	6U

Internal Aluminum Chassis Panel

Part No.	Overall Panel Dimensions			For use with Enclosure Dimensions	
	Height	Width	Depth	Width	Depth
RMP908	0.50	8.22	6.00	8.50	8.00
RMP1908	0.50	16.72	6.00	17.00	8.00
RMP1913	0.50	16.72	11.00	17.00	13.00
RMP1915	0.50	16.72	13.00	17.00	15.00

Data subject to change without notice